

# Other Measuring Devices

## Screw Pitch Gauges

- for internal and external measurements of threads
- fine cutted threads





| ART N° | quantity of blades | mm / inch                  | thread type       | graduation                                                                                                                    |                                                                                                                                 |
|--------|--------------------|----------------------------|-------------------|-------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| 471009 | 24                 | 0.25 – 6 mm                | metr. 60°         | 6 / 5.5 / 5 / 4.5 / 4 / 3.5 / 3 / 2.5 / 2 / 1.75 / 1.5 / 1.25                                                                 | 1 / 0.9 / 0.8 / 0.75 / 0.7 / 0.6 / 0.5 / 0.45 / 0.4 / 0.35 / 0.3 / 0.25                                                         |
| 471010 | 20                 | 0.4 – 7 mm                 | metr. 60° SI      | 7 / 6.5 / 6 / 5.5 / 5 / 4.5 / 4 / 3.5 / 3 / 2.5                                                                               | 2 / 1.75 / 1.5 / 1.25 / 1 / 0.8 / 0.75 / 0.7 / 0.5 / 0.4                                                                        |
| 471011 | 20                 | 4 – 30 Gang / t.p.i.       | whitw. 55°        | 4 / 4.5 / 5 / 6 / 7 / 8 / 9 / 10 / 11 / 12                                                                                    | 13 / 14 / 16 / 18 / 19 / 22 / 24 / 26 / 28 / 30                                                                                 |
| 471012 | 28                 | 4 – 62 Gang / t.p.i.       | whitw. 55°        | 4 / 4.5 / 5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 / 16 / 18                                                                | 19 / 20 / 22 / 24 / 25 / 26 / 28 / 30 / 32 / 36 / 40 / 48 / 60 / 62                                                             |
| 471013 | 48                 | 4 – 62 mm / 0.4 – 7        | whitw. / metr. SI | combined                                                                                                                      | Art. no.: 471012 + 471010                                                                                                       |
| 471014 | 52                 | 4 – 62 / 0.25 – 6          | whitw. / metr.    | combined                                                                                                                      | Art. no.: 471012 + 471009                                                                                                       |
| 471015 | 6                  | 8 – 28 Gang / t.p.i.       | whitw. 55°        | Tube                                                                                                                          | 8 / 10 / 11 / 14 / 19 / 28                                                                                                      |
| 471016 | 58                 | 4 – 62 / 0.25 – 6 / 8 – 28 | whitw. / metr.    | combined                                                                                                                      | Art. no.: 471014 + 471015                                                                                                       |
| 471017 | 14                 | 10 – 40 Gang / t.p.i.      | US 60° SAE        | 10 / 11 / 12 / 13 / 14 / 16 / 18                                                                                              | 20 / 24 / 27 / 28 / 32 / 36 / 40                                                                                                |
| 471018 | 30                 | 6 – 60 Gang / t.p.i.       | US 60° SAE        | 6 / 7 / 8 / 9 / 10 / 11 / 11.5 / 13 / 14 / 15 / 16 / 18 / 20 / 22 / 24                                                        | 26 / 28 / 30 / 32 / 34 / 36 / 38 / 40 / 42 / 44 / 46 / 48 / 50 / 56 / 60                                                        |
| 471019 | 30                 | 4 – 42 Gang / t.p.i.       | US 60° SAE        | 4 / 4.5 / 5 / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 11.5 / 12 / 13 / 14 / 15                                                        | 16 / 18 / 20 / 22 / 24 / 26 / 27 / 28 / 30 / 32 / 34 / 36 / 38 / 40 / 42                                                        |
| 471020 | 52                 | 4 – 84 Gang / t.p.i.       | US 60° SAE        | 4 / 4.5 / 5 / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 11.5 / 12 / 13 / 14 / 15 / 16 / 18 / 20 / 22 / 24 / 25 / 26 / 27 / 28 / 30 / 32 | 34 / 36 / 38 / 40 / 42 / 44 / 46 / 48 / 50 / 52 / 54 / 56 / 58 / 60 / 62 / 64 / 66 / 68 / 70 / 72 / 74 / 76 / 78 / 80 / 82 / 84 |
| 471021 | 22                 | 4 – 64 Gang / t.p.i.       | US 60° UNC        | 4 / 4.5 / 5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13                                                                               | 14 / 16 / 18 / 20 / 22 / 24 / 32 / 40 / 48 / 56 / 64                                                                            |
| 471022 | 16                 | 12 – 80 Gang / t.p.i.      | US 60° UNF        | 12 / 14 / 16 / 18 / 20 / 24 / 28 / 32                                                                                         | 36 / 40 / 44 / 48 / 56 / 64 / 72 / 80                                                                                           |

## Radius Gauges

- for testing of raised and recessed curves

- concave and convex shaped blades
- fine cutted forms




| ART N°<br>carbon steel | ART N°<br>stainless steel | quantity of blades | mm        | composition mm                                                                            |
|------------------------|---------------------------|--------------------|-----------|-------------------------------------------------------------------------------------------|
| 472105                 | 472115                    | 34                 | 1 – 7     | 1 / 1.25 / 1.5 / 1.75 / 2 / 2.25 / 2.5 / 2.75 / 3 / 3.5 / 4 / 4.5 / 5 / 5.5 / 6 / 6.5 / 7 |
| 472106                 | 472116                    | 32                 | 7.5 – 15  | 7.5 / 8 / 8.5 / 9 / 9.5 / 10 / 10.5 / 11 / 11.5 / 12 / 12.5 / 13 / 13.5 / 14 / 14.5 / 15  |
| 472107                 | 472117                    | 30                 | 15.5 – 25 | 15.5 / 16 / 16.5 / 17 / 17.5 / 18 / 18.5 / 19 / 19.5 / 20 / 21 / 22 / 23 / 24 / 25        |

## Radius Gauge Set

- matt chrome finish
- for testing of raised and recessed curves

- concave and convex shaped blades
- each blade with 5 measuring points



| ART N° | quantity of blades | mm       | composition mm                                                                                                                         |
|--------|--------------------|----------|----------------------------------------------------------------------------------------------------------------------------------------|
| 472109 | 26                 | 0.5 – 13 | 0.5 / 1 / 1.5 / 2 / 2.5 / 3 / 3.5 / 4 / 4.5 / 5 / 5.5 / 6 / 6.5 / 7 / 7.5 / 8 / 8.5 / 9 / 9.5 / 10 / 10.5 / 11 / 11.5 / 12 / 12.5 / 13 |