


Data Sheet

CY/CC 3 core 2.5mm 50M

Cross Section:



Description:

Rated Temperature (°C): -20 ~ 80
Rated Voltage (V): 300

Construction:

Conductor: Bare Copper
Conductor Dia. (mm): $0.25 \pm 0.008 \times 50$

Insulation: PVC

Insulation Dia. (mm): $3.4 \pm 0.1 \times 3C$

Tape Mylar: $\geq 115\%$

Braid Shield : Tinned Copper

Conductor Dia. (mm): 0.12

Conductor Qty: 16 x 10

Pitch(mm):

Coverage: 70%

Jacket: PVC

Outer Dia. (mm): 9.67 ± 0.2

Performance:

Electrical Characteristics:

Max. Conductor DC Resistance at 20°C (Ω/Km) :
<8.2

Min. Insulation DC Resistance at 20°C ($M\Omega \cdot \text{KM}$) :
>500

Current Rating : 20 A

Colour:

The color of the insulation: Blue , Brown , Yellow/Green

The jacket color: Grey (RAL-7001)

Marking(3times/m):

RS 522585 CY/CC 3 Core x 2.5mm²

