



## Prism Pro Fire Rated Downlight Warm White



- IP65 dimmable LED Fire Rated Downlight suitable for residential and hospitality applications
- Remote driver with 2x1.5mm<sup>2</sup> + CPC loop-in, loop-out colour coded push fit piano terminals provide an easy and efficient installation
- Detachable LED driver for fast fix install
- Low profile design and remote driver allows installation into shallow ceiling voids
- Fully tested for 30, 60 and 90 minute ceiling types to meet Part B of building regulations
- Fully tested to meet Part C (moisture), Part E (acoustic) and Part L (energy) of Building Regulations
- Wide 60° beam angle for increased light distribution

### General Information

|                                |                                    |
|--------------------------------|------------------------------------|
| Lamp Type                      | LED                                |
| Dimmable                       | Yes                                |
| Fire Rated                     | Yes                                |
| IP Rating                      | IP65                               |
| Class Protection               | 2                                  |
| Internal / External            | Internal                           |
| Surface / Recessed / Suspended | Recessed                           |
| OCTO Category                  | OCTO compatible powered by Casambi |



|                       |                          |
|-----------------------|--------------------------|
| Bluetooth Enabled     | Yes                      |
| Warranty (Years)      | 5                        |
| Material              | Aluminium, Polycarbonate |
| Technical Information |                          |
| Wattage               | 6W                       |
| Lumens Delivered      | 530lm                    |
| Lm/W                  | 89lm/W                   |
| Beam Angle            | 60                       |
| CRI                   | 80                       |
| CCT                   | 3000K                    |
| Input                 | 220/240V                 |
| Hertz                 | 50/60Hz                  |
| Operating Temp        | -5°C to 25°C             |
| Lumen Depreciation    | L70 60,000h              |
| Power Factor          | 0.9                      |



