

US-EMP (27,9X17,4) SR - Snap-in markers



0803300

<https://www.phoenixcontact.com/gb/products/0803300>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Snap-in markers, Card, silver, unlabeled, can be labeled with: THERMOMARK CARD, THERMOMARK CARD 2.0, THERMOMARK PRIME, BLUEMARK ID, BLUEMARK ID COLOR, THERMOMARK PRIME 2.0, mounting type: latching, Number of individual labels: 21, text field height: 17.4 mm, text field width: 27.9 mm

Your advantages

- All US-EMP ... device markers can also be supplied labeled according to customer requirements
- The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts

Commercial data

Item number	0803300
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2419
Product key	BG2419
Catalog page	Page 317 (C-3-2019)
GTIN	4055626020679
Weight per piece (including packing)	14.57 g
Weight per piece (excluding packing)	14.57 g
Customs tariff number	39204910
Country of origin	DE

US-EMP (27,9X17,4) SR - Snap-in markers



0803300

<https://www.phoenixcontact.com/gb/products/0803300>

Technical data

Product properties

Product type	Device marking
Marking	
Number of individual labels	21
Number of individual labels per row	3
Identification technology	Thermal transfer for sheets and cards

Mounting

Mounting type	latching
---------------	----------

Material specifications

Color	silver-colored
Material	PVC
	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

US-EMP (27,9X17,4) SR - Snap-in markers



0803300

<https://www.phoenixcontact.com/gb/products/0803300>

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	27.9 mm
Depth	0.5 mm
Length	17.4 mm
Material strength	0.50 mm

Text field

Text field width	27.9 mm
Text field height	17.4 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

US-EMP (27,9X17,4) SR - Snap-in markers



0803300

<https://www.phoenixcontact.com/gb/products/0803300>

Classifications

ECLASS

ECLASS-11.0	27281106
ECLASS-12.0	27281106
ECLASS-13.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

US-EMP (27,9X17,4) SR - Snap-in markers



0803300
<https://www.phoenixcontact.com/gb/products/0803300>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk