



Identification & Labeling > Pre-Printed Markers > STD Snap-On Markers



Marker Style: **Snap-On**

Marker Size: **STD 09**

Compatible Cable Diameter Range: **3.2 – 4.5 mm [.126 – .177 in]**

Primary Product Color: **Yellow**

Marker Cut: **Straight**

[All STD Snap-On Markers \(957\)](#)

Features

Body Features

Marker Style	Snap-On
Marker Size	STD 09
Primary Product Color	Yellow
Primary Product Material	Polyoxymethylene

Dimensions

Compatible Cable Diameter Range	3.2 – 4.5 mm[.126 – .177 in]
---------------------------------	------------------------------

Printer/Label Features

Marker Cut	Straight
Marking Details	Y

Packaging Features

Packaging Method	Strip
Packaging Quantity	300

Other

Printed Marking Color	Black
-----------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 007980-000
STD09Y-7

Also in the Series | Agastat 7000

A white rectangular AC relay with multiple gold-colored pins on one side and a black terminal block on the other.

AC Relays(8)

A collection of snap-on pre-printed markers, including a long orange one with many small white circles and a yellow one with a black 'K' marking.

Pre-Printed Markers(957)

A black and silver time delay relay with a black rotary knob on top and several terminals on the bottom.

Time Delay Relays(41)

Customers Also Bought

A black plastic connector assembly with a grid of pins.

TE Part #1473244-3
MQS/JPT 81POS PLUG ASSY

A stack of three white cable strain relief boots with black markings.

TE Part #5070112026
RNF-100-1-1/2-X-STK

A red cylindrical spade terminal with a silver metal fork-like contact.

TE Part #130517
PIDG 22-16 SPADE M4

Two orange cylindrical components, one with a silver band.

TE Part #590428-000
BPTM-15/6-A/U-4(S30)

A black cylindrical cavity plug with a silver metal contact.

TE Part #936054-1
CAVITY PLUG(ECU 40P&81P ASSY)

A cross-sectional diagram of a plug and a side view of a plug with two circular openings.

TE Part #1-350344-0
02P .140 MNL PLUG NAT

A close-up of a multi-pin connector with yellow and blue pins.

TE Part #1056030001
D-SCE-1K-3.2-50-S1-4

A black cylindrical component with a silver metal band.

TE Part #738430-000
202K163-3/86-0

A cross-sectional diagram of a dielectric material with a metal contact.

TE Part #4-1579001-6
ERGO DIE MCP 1,2 LL EDS

A white plastic component with a grid of pins.

TE Part #172506-1
MIC CAP HSG 9P MK II

Documents

Product Drawings

STD09Y-Y

English

Datasheets & Catalog Pages

STD/STB-type Snap-on Pre-printed Wire & Cable Markers

English

IDENTIFICATION SELECTION GUIDE

English



STD and STB Technical Datasheet

English

Product Specifications

RW-2538 STD and STB work instruction

English