

Garden Sprayer LXT®

DUS054

18V • 5 L

Battery-operated for easy setup and lightweight carrying.

Garden Sprayer powered by an 18V battery. Easy to set up and light to carry. Very quiet running sound. Two nozzles.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Maximum Flow Rate	0,91 L/min
Max Pressure	3 bar
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,2 - 3,5 kg
Product Dimensions (L x W x H):	343 x 182 x 368 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Hose length	1,7 m
Product net weight	2,8 kg
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Container Capacity	5 L

User benefits

- Dust and water resistance with IP54 rating for increased durability
- Large spray volume on a single full battery charge
- Battery protection system automatically shuts off power when the battery level is low
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing