



06160040

RCK 16 - Self centring

2D Technical Drawing



Dynamic 3D View



Technical Specifications

Part number (CODE)	06160040
Ød (DD) mm	40
ØD (D) mm	65
L1 (L1) mm	17
L2 (L2) mm	22
L3 (L3) mm	28
L (L) mm	34
Maximum torque Mt (MT) Nm	900
Clamping pressure - Shaft (CPS) N/mm ²	175
Clamping pressure - Hub (CPH) N/mm ²	105
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	8
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M6x20
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	17
Extraction thread - Type (ETT)	M6
Extraction thread - Num. (ETN)	4
Weight (WEIGHT) kg	0.50