

1613786
<https://www.phoenixcontact.com/gb/products/1613786>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, angled fixed, Screw locking mechanism, M23, number of positions: 16, contact connection type: Socket, Axial O-ring, shielded: yes, flange dimensions: 26 mm x 26 mm, number of positions: 16, connection method: Crimp connection, series: RF

Commercial data

Item number	1613786
Packing unit	16 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	ABRAGM
Product key	ABRAGM
GTIN	4046356402309
Weight per piece (including packing)	132.437 g
Weight per piece (excluding packing)	117.448 g
Customs tariff number	85366990
Country of origin	DE

RF-16S1N8AAF00 - Device connector front mounting



1613786

<https://www.phoenixcontact.com/gb/products/1613786>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Mounting

Mounting type	Front mounting/square flange 4x Ø 3,2 mm
Assembly note	4x Ø 3,2 mm

Product properties

Product type	Circular connectors (device side)
Series	RF
Application	Signal
	Signal
Number of positions	16
Connection profile	16
Shielded	yes
Coding	N
Thread type	M23

Dimensions

Housing

Flange dimensions	26 mm x 26 mm
-------------------	---------------

Material specifications

Flammability rating according to UL 94	V0
Seal material	FPM
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Gasket and O-ring material	FPM

Electrical properties

Contact

Contact diameter	1 mm
Max. current	8 A
Nominal voltage U_N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

RF-16S1N8AAF00 - Device connector front mounting



1613786

<https://www.phoenixcontact.com/gb/products/1613786>

Connection method	Crimp connection
Contact connection type	Socket

Connector

Type	angled fixed
Direction of rotation	Standard


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	2000 m


Drawings

Dimensional drawing



Installation dimensions

Dimensional drawing




Dimensional drawing

1613786

<https://www.phoenixcontact.com/gb/products/1613786>

Schematic diagram



Connector pin assignment

RF-16S1N8AAF00 - Device connector front mounting





1613786

<https://www.phoenixcontact.com/gb/products/1613786>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1613786>

	cUL Recognized Approval ID: E153698-20090723			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	1 A	26	-

	UL Recognized Approval ID: E153698-20090723			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	1 A	26	-

RF-16S1N8AAF00 - Device connector front mounting



1613786

<https://www.phoenixcontact.com/gb/products/1613786>

Classifications

ECLASS

ECLASS-13.0	27440109
-------------	----------

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RF-16S1N8AAF00 - Device connector front mounting



1613786

<https://www.phoenixcontact.com/gb/products/1613786>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk