

FEATURES

- **Graphite material:** Provides excellent thermal conductivity and chemical resistance
- **Maximum operating pressure of 20000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 650 °C:** Ensures performance in extreme heat conditions
- **Rotary speed of 30 m/s:** Supports high-speed applications
- **3.2 mm section:** Offers precise fitting for various gland and valve sizes

RS PRO 8m Graphite Gland & Valve Packing, 3.2mm Section

RS Stock No: 606-569



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland and valve packing is designed for high-performance sealing applications. Made from durable graphite, it is ideal for use in environments requiring high temperature and pressure resistance. Its primary benefit is ensuring reliable sealing in industrial systems, reducing leakage and maintenance needs.

General Specifications

Maximum Operating Pressure	20000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	30 m/s
Section	3.2 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Graphite

Operation Environment Specifications

Maximum Operating Temperature	650 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------