

### product type designation

**SFP992-1BXMT**

SCALANCE X accessory; Plug-in transceiver SFP992-1BXMT; 1x 1000 Mbit/s LC port, optical; multimode optical up to max. 500 m BiDi Transceiver 1550 nm/1310 nm.



interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	1
number of optical interfaces / for network components or terminal equipment / maximum	1
number of 1000 Mbit/s LC ports / for multimode / integrated	1
design of the optical interface / for network components or terminal equipment	LC
wavelength / of the optical interface	1550 nm; Multi-mode
<ul style="list-style-type: none"> <li>• as transmitter</li> <li>• as receiver</li> </ul>	1550 nm 1310 nm
connectable optical power relative to 1 mW	
<ul style="list-style-type: none"> <li>• of the transmitter output / minimum</li> <li>• of the transmitter output / maximum</li> <li>• of the receiver input / maximum</li> </ul>	-10 dB -4 dB -3 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-17 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0 ... 0.5 km
transmission method / for connection type 1	1000BASE-BX
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> <li>• during transport</li> </ul>	-40 ... +85 °C -40 ... +85 °C -40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	SFP Module
width	14 mm
height	9 mm
depth	57 mm
net weight	0.01 kg
fastening method	latched
standards, specifications, approvals	
standard	
<ul style="list-style-type: none"> <li>• for hazardous zone</li> </ul>	EN 60079-0: 2011, EN60079-15: 2010, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X

<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> <li>• for emitted interference</li> <li>• for interference immunity</li> </ul>	UL 60950-1, CSA C22.2 No. 60950-1-03 EN 61000-6-4:2007 (Class A) EN 61000-6-2:2005
certificate of suitability <ul style="list-style-type: none"> <li>• CE marking</li> <li>• C-Tick</li> <li>• KC approval</li> <li>• CCC / for hazardous zone according to GB standard</li> <li>• CCC / for hazardous zone according to GB standard / as marking</li> </ul>	EN 61000-6-2:2005, EN 61000-6-4:2007 Yes Yes No Yes; GB3836.1, GB3836.8 Ex nA IIC T4 Gc
MTBF	340 a
<b>further information / internet links</b>	
internet link <ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> <li>• to website: Industrial communication</li> <li>• to website: Industry Mall</li> <li>• to website: Information and Download Center</li> <li>• to website: Image database</li> <li>• to website: CAX-Download-Manager</li> <li>• to website: Industry Online Support</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a> <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a> <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a> <a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a> <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a> <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a> <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

**last modified:**

11/9/2023 