

VB: 32 mm, 3W, Globe, Rp Int, BR, 16 kvs, Glycol 25-50% and Water, Venta, No Steam

7311737000

EAN Code: 3606489658731

### Main

***************************************		
Valve product range	Venta	
Product or component type	Valve	
Valve type	Globe	
Valve product series	V311T	
Valve model	V311T/32/16	
Medium compatibility	Glycol 25 % Glycol 30 % Glycol 50 % Water	
Valve configuration	3-Way	
Valve connection type	Rp Internal	
Valve connection size	Rp 1-1/4	
Body size	32 mm (1-1/4 in)	
Pipe size	32 mm	
Flow characteristic	Equal percentage	
Flow coefficient	18.5 cv 16 kvs	
Pressure class	PN16	
Operating fluid temperature	-20120 °C	
Pressure fluid max delta P normal life	399.9 kPa	
Control valve rangeability	Greater than 50:1	
Stroke length	20 mm	
Seat leakage	Port A: Class IV-S1 (0.005 %)	
Stem flow action	Stem up closes A and opens B to AB	
Stem movement	Linear	
Trim material	Brass	
Body material	Nodular cast iron EN-JS 1030	
Seat material	Port A: nodular cast iron EN-JS 1030 Port B: nodular cast iron EN-JS 1030	
Stem material	Stainless steel AISI 303	
Plug material	CW602N brass	
Stem seal material	EPDM (ethylene propylene diene monomer)	
Seating seal material	Port A:EPDM (ethylene propylene diene monomer) Port B:EPDM (ethylene propylene diene monomer)	

Packing material	EPDM (ethylene propylene diene monomer)
Targeted region	Europe Asia Pacific.
	Australia.

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.9 cm
Package 1 Width	20.9 cm
Package 1 Length	7.3 cm
Package 1 Weight	1.92 kg

# Logistical informations

Country of origin S

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

### Environmental Data explained >

How we assess product sustainability

∅ Environmental fellow	ootprint
------------------------	----------

Environmental Disclosure Product Environmental Profile

### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No