

DATASHEET - NH2 SINGLE POLE PV



Fuse base, high speed, 400 A, AC 690 V, 50 kA, NH2, 1P, IEC, UL, CSA

Part no. NH2 SINGLE POLE PV
Catalog No. SD2-D-PV



Similar to illustration

Delivery program

Product range			Fuse accessory
Basic function			Fuse-base
Field of application			high speed
Rated current	I	A	400
Rated voltage			AC 690 V
Construction size			NH2
Breaking Capacity		kA	50
Number of poles			1P
usable for size/applications			NH Photovoltaic fuse links
Standard/Approval			IEC UL CSA
Material			Glass-filled PBT body
Standards/Regulations			IEC 60269-1
Optional accessories			Microswitches, Shroud kit, Phase barriers, Neutral links and Fuse extraction handle

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse base (EC000067)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Low-Voltage HRC fuse base (ecI@ss10.0.1-27-14-21-06 [AKE278013])			
Construction size			NH2
Number of poles			1
Rated current		A	400
Bus-mounting type			Yes
Swivelling mechanism			Yes