



EN ISO 20344:2011



ATLANTIDA
STELVIO
80087-01L

S3 *CI HRO HI SRC

Size: 38-48
Weight: 765 gr.

Fit: 11

Working Environment:
Building, Wood-metal carpentry,
Engineering, Farming and
Gardening



FEATURES

UPPER

Greased Nubuk Dakar Leather
Hydro 1,8-2,0 mm
Full Grain Leather Hydro

LINING

3D Air circulation 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Climaction-Fit 337

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Ankle boot

SOLE

PU-RUBBER VIBRAM-HRO

Sole with anti-wear scaff cap.
Outsole in VIBRAM rubber,
resistant to 300° C by contact
(HRO), to acids and oils. Design
with self-cleaning outsole, with
Antislip standard.

TECHNOLOGIES

Removable Insole

337
climaction fit

Removable anatomic and ergonomic
insole. Absorbent and transpiring
open-cell foam support. Keeps feet
fresh. Specifically-designed
thermoforming for exceptional
comfort.



Protection elements

KX RESISTANT TO 3.0 mm. NAILS **fibercap sxt**

Composite toecap with fiberglass.
Resistant to over 200J. Non metal
perforation resistant insert to over
1100 N with a 3.0 mm truncated cone
nail. Protection over the entire sole of
the foot. Flexible and comfortable



Lateral stability

dynamic control
technology

Ergonomic rigid structure. It
accommodates the heel, adjusting the
foot support and control of the ankle
in sideways movements. The plastic
material increases protection of the
ankle against sharp or pointy objects.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic
material. It stabilizes the heel bone,
the instep and tarsal joints, without
altering energy absorption. A support
for the natural movement of the foot;
it provides comfort and greater
stability.




Electrical features

WED

Wire Electricity Discharge

Strip with 4 filaments of carbon fiber,
ensuring proven anti-static properties
of the footwear over time.



Other

DUALMICRO
DUALMICRO

Double non-slip layer of microfibre,
resistant up to 200,000 cycles. Makes
the footwear more comfortable,
blocking the foot during use.



SRC (SRA+SRB)



		SOLE 80 PU - RUBBER
SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE 7°) ≥0.28	0.43 0.35
SRB STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE 7°) ≥0.13	0.19 0.13

EN ISO 20344:2011