

Push-to-test pilot light, Harmony XB4, metal, amber, universal LED, screw clamp terminals, 110...120V

Local distributor code:

409067699

XB4BW28G5

Important message: A change in appearance may be noted on the product but does not affect its use in terms of function and safety. This makes it compatible with our Universal LED blocks EAN Code: 3606489420673

Main

Range of product	Harmony XB4	
Product or component type	Push-to-test pilot light	
Device short name	XB4	
Bezel material	Metal	

Complementary

Metal	
22.5 mm	
1	
42 mm	
30 mm	
55 mm	
0.09 kg	
7000000 Pa at 55 °C, distance : 0.1 m	
43 mm	
Round	
Amber	
Screw clamp terminals, <= 2 x 1.5 mm² with cable end conforming to IEC 60068-2-27 Screw clamp terminals, 1 x 0.222 x 2.5 mm² without cable end conforming to IEC 60068-2-27	
0.81.2 N.m conforming to IEC 60947-1	
600 V (pollution degree 3) conforming to IEC 60947-1	
6 kV conforming to IEC 60947-1	
Steady	
Universal LED	
Amber	
14 mA	
1.5 year(s)	
1 kV	
110120 V AC at 50/60 Hz	

Environment

Protective treatment	тн	
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-4070 °C	
Overvoltage category	Class II conforming to IEC 60536	
IP degree of protection	IP66 conforming to IEC 60536 IP67 IP69 IP69K	
NEMA degree of protection	NEMA 13 conforming to IEC 60529 NEMA 4X	
IK degree of protection	IK05 conforming to IEC 50102	
Standards	CSA C22.2 No 14 IEC 60947-1 IEC 60947-5-1 IEC 60947-5-4 GB 14048.5 JIS C8201-5-1 UL 508 JIS C8201-1	
Product certifications	CSA LROS (Lloyds register of shipping) BV UL listed DNV	
Vibration resistance	5 gn (f= 12500 Hz) conforming to IEC 60068-2-6	
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-6 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-6	

Packing Units

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	4.3 cm
Package 1 Length	5.2 cm
Package 1 Weight	100.0 g

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	425812e5-011f-4fb4-ad1b-fc9cf9865300
REACh Regulation	REACh Declaration

Use Again


○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product datasheet

XB4BW28G5

Dimensions Drawings

Dimensions




- $\boldsymbol{e}\text{:}$ Panel thickness: 1 mm to 6 mm / 0.04 in. to 0.24 in (1) Side view
- (2) Top view

XB4BW28G5

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)



- **(4)** Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $_0^{+0.4}$ / 0.88 in. $_0^{+0.016}$)
- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.

XB4BW28G5

Technical Illustration

Dimensions

