

D-SCE-1K-9.5-50-S1-9

✓ ACTIVE

TE Internal #: 412575-000
Ladder, Fluid Resistant, 3:1, White, 1 Prescores, 2 Markers per Sleeve, 25 mm [1 in] Length, 9.5 mm [.375 in] Expanded Inside, Printable Tubing
[View on TE.com >](#)



Identification & Labeling > Printable Tubing > D-SCE Fluid Resistant Sleeves



Printable Tubing Type: **Ladder**
Printable Tubing Grade: **Fluid Resistant**
Shrink Ratio: **3:1**
Primary Product Color: **White**
Number of Prescores: **1**

[All D-SCE Fluid Resistant Sleeves \(65\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Fluid Resistant

Body Features

Shrink Ratio	3:1
Primary Product Color	White
Markers per Sleeve	2

Dimensions

Product Length	25 mm[1 in]
Expanded Inside Diameter (Min)	9.5 mm[.375 in]
Recovered Inside Diameter (Max)	3.2 mm[.13 in]
Compatible Cable Diameter Range	3.4 – 8.1 mm[.136 – .319 in]

Usage Conditions

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

Printer/Label Features

Printer Technology	Thermal Transfer
Number of Prescores	1



Packaging Features

Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # F55931-000
1966-RIBBON



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
[T3224-SWARE-PRINTER](#)

TE Part # 311292-000
[TMS-RJS-RIBBON-4DSCE](#)

Customers Also Bought

TE Part #CAT-R21-T7907
Single Wall DR 25: Heat Shrink Tubing,
2:1 Shrink Ratio

TE Part #405309-000
[D-SCE-1K-12-50-S1-9](#)

TE Part #CAT-R21-731072
Bulbous Heat Shrink Boots: Lipped,
Straight

TE Part #CX9423-000
[DR-25-3/8-0-200FT/CSP](#)

Documents

- Datasheets & Catalog Pages

[IDENTIFICATION SELECTION GUIDE](#)

English

[D-SCE Heat Shrink Identification Sleeves](#)

English

- Product Specifications

[Product Specification](#)

English

[IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX](#)

English

- Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English