


PCH-112D2H,000

OEG

TE Internal #: 9-1440003-3

TE Internal Description: PCH-112D2H,000

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 9-1440003-1
[PCH-106D2H,000](#)

TE Part # 1721766-5
[PCH-112D2-WG](#)

TE Part # 1461410-2
[PCH-148D2,000](#)

TE Part # 1440004
[PCH-112D2,000](#)

TE Part # 9-1440003-2
[PCH-109D2H,000](#)

TE Part # 9-1440003-5
[PCH-124D2H,000](#)

TE Part # 9-1440003-9
[PCH-109D2,000](#)

TE Part # 1721767-5
[PCH-112D2M-WG](#)

TE Part # 9-1440003-8
[PCH-106D2,000](#)

TE Part # 1461351-6
[PCH-124D2MH,000](#)

TE Part # 1461410-3
[PCH-118D2H,000](#)

TE Part # 1461410-4
[PCH-148D2H,000](#)

TE Part # 1440004-1
[PCH-124D2,000](#)

TE Part # 1461350-5
[PCH-112D2M,000](#)

TE Part # 9-1440003-0
[PCH-105D2H,000](#)

TE Part # 9-1440003-7
[PCH-105D2,000](#)

Customers Also Bought

TE Part #4-794630-6
[16P MICRO MNL ASSY,VRT,HDR,LF](#)

TE Part #CAT-OE4-OJ1
[STD OEG Miniature PCB OJ/OJE Pow Relays](#)

TE Part #4-1419172-4
[V23101D 6A301](#)

TE Part #1-1623730-5
[BCHE 4 W 33R 5%](#)



TE Part #1721441-5
PCN-112D3MHZ,001B




TE Part #1734101-7
Champ050 series,68pos,Au over PdNi



TE Part #2-1879022-1
SMF3 2K2 5%



TE Part #2-2176309-8
RP 1E 0.1W 19R1 0.1% 25PPM 1K RL



TE Part #2071369-3
OJE-SH-112DM,00E3W

Documents

Product Drawings

PCH-112D2H,000

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-1440003-3_E1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-1440003-3_E1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-1440003-3_E1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PCH Series Relay Data Sheet - English

English

Product Specifications

PCH-112D2H,001 Spec Sheet

Japanese

PCH TRAY PACKING

English



Definitions General Purpose Relays

English