

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: Sunnex

Supplier's address: Product, Körkarlsvägen 4, 65346 Karlstad, SE

Model identifier: TELLUS

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	12-24V AC/DC		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	Yes		
Anti-glare shield:	No	Dimmable:	Only with specific dimmers

Product parameters

Parameter	Value	Parameter	Value
-----------	-------	-----------	-------

General product parameters:

Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	4	Energy efficiency class	G
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	300 in Narrow cone (90°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	4 000
On-mode power (P_{on}), expressed in W	4,2	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	90
Outer dimensions without separate control gear, light-	Height	680	Spectral power distribution in the range 250 nm to 800 nm, at full-load
	Width	60	
	Depth	60	
			See image in last page


ing control parts and non-lighting control parts, if any (millimetre)			
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-
		Chromaticity coordinates (x and y)	0,390 0,394
Parameters for directional light sources:			
Peak luminous intensity (cd)	2 635	Beam angle in degrees, or the range of beam angles that can be set	15
Parameters for LED and OLED light sources:			
R9 colour rendering index value	90	Survival factor	0,95
the lumen maintenance factor	1,00		

(a)¹⁾ : not applicable;


(b)¹⁾ : not applicable;

Spectrum

1.0 = 4.708e+000mW/nm



Model placed on the Union market from 29/05/2017



EPREL registration number: 1482114

<https://eprel.ec.europa.eu/qr/1482114>

Supplier: Sunnex Equipment AB (Manufacturer)

Website: www.sunnex.se

Customer care service:

Name: Product

Website: www.sunnex.se

Email: torbjorn.andersson@sunnex.se

Phone: +4654555162

Address:

Körkarlsvägen 4
65346 Karlstad
Sweden