



auxiliary switch, solid-state compatible, on the front, 2 NO + 1 NC, .3/.4, --/--, .3/.4, .1/.2, current path: 1 NO (solid-state compatible), --, 1 NO, 1 NC (solid-state compatible), spring-loaded terminal, for contactors 3RT2 and contactor relays 3RH2

product brand name	SIRIUS
product category	Auxiliary switch
product designation	auxiliary switch
design of the product	for snapping onto the front
product type designation	3RH29
suitability for use	for 3RT2.1, 3RT2.2, 3RT2.3, 3RT2.4, 3RH2
General technical data	
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
protection class IP on the front	IP20
mechanical service life (operating cycles) typical	5 000 000
Substance Prohibitance (Date)	10/01/2009
Net Weight	0.056 kg
number of NC contacts for auxiliary contacts	
• instantaneous contact	1
• lagging switching	0
number of NO contacts for auxiliary contacts	
• instantaneous contact	2
• leading contact	0
number of CO contacts of auxiliary contacts instantaneous contact	0
operational current of auxiliary contacts at DC-13	
• at 24 V	0.3 A
• at 48 V	0.3 A
• at 60 V	0.3 A
design of the miniature circuit breaker for short-circuit protection of the auxiliary circuit up to 230 V	conventional: C characteristic: 10 A; 0.4 kA
contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (5 V, 1 mA)
Ambient conditions	
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-55 ... +80 °C
Safety related data	
product function	
• mirror contact according to IEC 60947-4-1	Yes; with 3RT2.2/3/4
• positively driven operation according to IEC 60947-5-1	No
Short-circuit protection	
design of the miniature circuit breaker for short-circuit protection of the auxiliary circuit up to 230 V	conventional: C characteristic: 10 A; 0.4 kA

design of the fuse link for short-circuit protection of the auxiliary switch required		conventional: gG: 10 A (690 V, 1 kA); electronically optimized: FF microfuse 2 A (250 V, 1 kA)	
Installation/ mounting/ dimensions			
fastening method		snap-on mounting	
height		41.5 mm	
width		36 mm	
depth		47.7 mm	
Connections/ Terminals			
type of electrical connection for auxiliary and control circuit		spring-loaded terminals	
connectable conductor cross-section for auxiliary contacts			
• solid or stranded		0.5 ... 2.5 mm²	
• finely stranded with core end processing		0.5 ... 2.5 mm²	
• finely stranded without core end processing		0.5 ... 2.5 mm²	
type of connectable conductor cross-sections			
• for auxiliary contacts			
— solid or stranded		2x (0.5 ... 2.5 mm²)	
— finely stranded with core end processing		2x (0.5 ... 1.5 mm²)	
— finely stranded without core end processing		2x (0.5 ... 2.5 mm²)	
• for AWG cables for auxiliary contacts		2x (20 ... 14)	
AWG number as coded connectable conductor cross section for auxiliary contacts		20 ... 14	
Approvals Certificates			
Environmental Product Declaration			
• global warming potential [CO2 eq] / during manufacturing		0.375 kg	
• global warming potential [CO2 eq] / during operation		0.00141 kg	
• global warming potential [CO2 eq] / after end of life		0.0202 kg	
• global warming potential [CO2 eq] / total		0.397 kg	
Environment		General Product Approval	
			
Environmental Confirmations			
			
			
General Product Approval		EMV	
			
		Type Examination Certificate	
		Special Test Certificate	
		Type Test Certificates/Test Report	
			
Maritime application			
			
			
			
			
			
			
other		Railway	
Miscellaneous		Confirmation	
		Type Test Certificates/Test Report	
		Special Test Certificate	

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RH2911-2NE21>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RH2911-2NE21>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/3RH2911-2NE21>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RH2911-2NE21&lang=en




3RT2x1



3RT2x2 / 3RT2x3 / 3RT2x4



3RH2



last modified:

6/1/2025