



Main

Range	Thorsman
Range of product	Thorsman Worklights
Product name	Worklight
Product or component type	Lamp
Device application	Mobile equipment Ware-houses and parking garages Hospital Residential Sports hall

Complementary

Type of installation	Outdoor
[Ue] rated operational voltage	230 V
Network type	AC
Operational power in W	30 W
Plug standard	Contour
Luminous flux	3000 lm
Bulb lifespan	50000 h
Colour rendering index	R _a =80
Colour temperature	4000 K
Beam angle	110 °
Power factor	0.9
Height	254.5 mm
Width	231.0 mm
Depth	20.0 mm
Net weight	1.1 kg

Environment

Environmental characteristic	Water resistant Dust resistant UV resistant Impact resistant
IP degree of protection	IP65
Ambient air temperature for operation	-30...45 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.7 kg
Package 1 Height	26 cm
Package 1 width	26 cm
Package 1 Length	26 cm
Unit Type of Package 2	S03
Number of Units in Package 2	5
Package 2 Weight	8.941 kg
Package 2 Height	30 cm

Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Weight	155.056 kg
Package 3 Height	80 cm
Package 3 width	80 cm
Package 3 Length	120 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information