


LED Spot PAR38 ColourSwitch E27 12W RGB+827+865 1000lm 38°

Article number: 147140

BAI LED Spot PAR38 ColourSwitch E27 12W Switch Red Green Blue 75° + 2700K & 6500K 38° 1000lm 122x133mm Only the cover is IP44 LED-lamp

This colorful mood-enhancer from the BaiColour LED Spot series has been thoughtfully designed for professional use. Thanks to energy-efficient LED technology (only 12W) and a long average lifespan of 15.000 hours, it is a far more sustainable alternative to traditional colored PAR lamps. The integrated Switch function allows a single PAR38 lamp to replace five different light sources: red, green, blue, warm white (2700K), and cool white (6500K). This significantly reduces the number of lamps required, as well as transportation and inventory costs. Featuring a 38° beam angle and a light output of up to 1000 lumens (in white light modes), this lamp delivers powerful and consistent illumination. The standard E27 base ensures compatibility with a wide range of fixtures and pendant sets. Ideal for retail environments, showrooms, and event venues, and reliable within an ambient temperature range of -25°C to +40°C.



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	LED Spot PAR38 ColourSwitch E27 12W RGB+827+865 1000lm 38°
Brand	Bailey
Productseries	BaiColour LED spot
Producttype	PAR38 E27 RGBW

ETIM specifications

Socket	E27
Luminous flux [lm]	1000 - 1000
Nominal voltage [V]	220 - 240
Lamp power [W]	12 - 12
Colour temperature [K]	2700 - 6500
Diameter [mm]	122
Length [mm]	133
Dimmable	No
Lamp shape	Reflector
Beam angle [°]	38 - 38
Colour	White
Type of glass/cover	Prism
Lamp designation	PAR38
Colour rendering index CRI	80-89
Voltage type	AC
Filament lamp	No
Luminous intensity [cd]	1900
Power factor	0.5
Lamp efficacy [lm/W]	83
Nominal current [mA]	93 - 93
Housing colour	White
Average nominal lifetime [h]	15000
Degree of protection (IP)	IP44
Colour consistency (McAdam ellipse)	SDCM6
Min. number of switching cycles	7500
Weighted energy consumption in 1000 hours [kWh]	12
Remote operation possible	No
With movement sensor	No
With remote control	No
Photobiological safety according to EN 62471	RG1
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Suitable for electronic ballast	No
Suitable for magnetic ballast	No
Dimming phase cut-off (trailing edge)	No
Dimming phase cut-on (leading edge)	No
Dimming Touch and Dim	No
Dimming Zigbee	No
Dimming Bluetooth	No

Dimming Wi-Fi	No
Energy efficiency class according to EU regulation 2019/2015	F
With twilight switch	No

Alternative articles



146500
LED Spot PAR38 Glass E27 DIM 12W (120W) 1100lm 927 36° IP65



80100038767
LED PAR38 E27 100V-240V 15W Red