



PRODUCT-DETAILS

ESB20-11N-06

ESB20-11N-06 Installation Contactor (NC) 20 A - 1 NO - 1 NC - 230 V - Control Circuit DC



概要信息	
产品型号	ESB20-11N-06
产品ID	1SBE121111R0611
欧洲商品编号(EAN)	3471523007499
目录说明	ESB20-11N-06 Installation Contactor (NC) 20 A - 1 NO - 1 NC - 230 V - Control Circuit DC
详细描述	The ESB20..N installation contactors are used to control single loads up to 20 A and can be operated by AC or DC.
	These contactors are made for use in household applications as well as in industrial environments.
	The following benefits are provided:
	Hum-free operation, low power consumption and integrated overvoltage protection.
Various contact combinations and accessories are available.	

订货信息	
1级包装 EAN	3471523005389
最小起订量	1 piece
海关关税号	85365080

Popular Downloads	
数据手册，技术资料	2CDC103051C0201
说明书和手册	2CDC103043M6801
CAD Dimensional Drawing	2CDC001079B0201
尺寸图	1SBB505186D3001

尺寸	
产品净宽	18 mm
产品净高	85 mm
产品净深	65 mm
产品净重	0.14 kg

技术参数	
额定工作电压	Main Circuit 220 V DC Main Circuit 250 V AC
额定控制电路电压 (U _c)	230 V
额定频率 (f)	Control Circuit DC Control Circuit 50 Hz Control Circuit 60 Hz Control Circuit 400 Hz Main Circuit DC Main Circuit 50 Hz Main Circuit 60 Hz
额定工作电流 AC-1 (I _e)	(NC) 20 A (NO) 20 A
额定工作电流 AC-3 (I _e)	(230 V) Single Phase, NC 9 A (230 V) Single Phase, NO 9 A
额定工作功率 AC-1 (P _e)	(230 V) Single Phase, NC 4.6 kW (230 V) Single Phase, NO 4.6 kW
额定工作功率 AC-3 (P _e)	(230 V) Single Phase, NC 1.3 kW (230 V) Single Phase, NO 1.3 kW
额定工作电流 AC-7a (I _e)	(NC) 20 A (NO) 20 A
额定工作功率 AC-7a (P _e)	(230 V) Single Phase, NC 4.6 kW (230 V) Single Phase, NO 4.6 kW
额定工作电流 AC-7b (I _e)	(230 V) Single Phase, NC 9 A (230 V) Single Phase, NO 9 A
额定工作功率 AC-7b (P _e)	(230 V) Single Phase, NC 1.3 kW (230 V) Single Phase, NO 1.3 kW
推荐的螺丝刀	Control Circuit Pozidriv 1 Main Circuit Pozidriv 1
额定冲击耐受电压 (U _{imp})	6 kV
额定绝缘电压 (U _i)	400 V
主电路连接容量	Flexible with Ferrule 1x 1 ... 6 mm ² Flexible with Ferrule 2x 1 ... 2.5 mm ² Flexible with Insulated Ferrule 1x 1 ... 6 mm ² Flexible with Insulated Ferrule 2x 1 ... 1.5 mm ² Flexible 1x 1 ... 6 mm ² Flexible 2x 1 ... 4 mm ² Rigid 1x 1 ... 10 mm ² Rigid 2x 1 ... 4 mm ²
控制电路连接容量	Flexible with Ferrule 1x 1 ... 2.5 mm ² Flexible with Ferrule 2x 0.75 ... 1.5 mm ² Flexible with Insulated Ferrule 1x 1 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1 mm ² Flexible 1x 1 ... 2.5 mm ²

	Flexible 2x 1 ... 1.5 mm ² Rigid 1x 0.5 ... 4 mm ² Rigid 2x 0.75 ... 2.5 mm ²
拧紧力矩	Control Circuit 0.9 N·m Main Circuit 1.2 N·m
剥线长度	Control Circuit 7 mm Main Circuit 10 mm
防护等级	IP20
电气寿命	AC-1 (NC) 150000 cycle AC-1 (NO) 150000 cycle AC-3 (NC) 150000 cycle AC-3 (NO) 150000 cycle AC-7a (NC) 150000 cycle AC-7a (NO) 150000 cycle AC-7b (NC) 150000 cycle AC-7b (NO) 150000 cycle
机械寿命	1000000 cycle
极数	2P
辅助触点NC数量	0
辅助触点NO数量	0
主触点NC数量	1
主触点NO数量	1
宽度(模块化垫片数)	1.0
污染等级	3
标准	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1 IEC/EN 61095 IEC 60335-2-40 A2L

UL/CSA适用的技术参数

最高工作电压UL/CSA	Main Circuit 240 V AC
额定功率UL/CSA	(220 ... 240 V AC) Single Phase, NC 1 Hp (220 ... 240 V AC) Single Phase, NO 1 Hp
主电路连接容量 UL/CSA	Solid 14-8 AWG Stranded 14-8 AWG
控制电路连接容量 UL/CSA	Solid 16-10 AWG Stranded 16-10 AWG
拧紧力矩UL/CSA	Control Circuit 8 in·lb Main Circuit 11 in·lb

环境条件

周围环境温度	Operation -25 ... +55 °C Storage -40 ... +80 °C
允许的最高工作海拔	2000 m
抗机械冲击符合IEC 60068-2-27标准	11 ms Pulse 15g
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202

RoHS信息	2CMT2021-006277
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Consumer
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

ABB EcoSolutions

产品环境声明 - EPD	1SAC200416H0001
产品寿命终止后的拆解指南	1SBC100156C0268

认证及声明（文件编码）

A2L Certificate – IEC	1SAA920000-4601
ABS认证	1SAA920000-0101
CB认证	1SAA920007-2001
CQC认证	CQC2018010304057353 CQC2018010304057344
Declaration of Conformity - CCC	2020980304001370 2020980304001371
符合性声明 - CE	1SAD101100-3301
Declaration of Conformity - UKCA	1SAD201100-3301
DNV认证	1SAA920000-0306
EAC认证	1SAA920003-2701
RMRS认证	1SAA920000-0705
UL认证	E191658-19960301

包装信息

1级包装单元	box 1 piece
1级包装宽度	88 mm
1级包装高度	71 mm
1级包装长度	20 mm
1级包装 总重	0.14 kg

分类

对象分类代码	Q
ETIM 5	EC001653 - Installation contactor for distribution board
ETIM 6	EC001653 - Installation contactor for distribution board
ETIM 7	EC001653 - Installation contactor for distribution board
e级	V11.0 : 27142308
UNSPSC	39121529
IDEA 粒度分类代码 (IGCC)	4759 >> Installation contactor for distribution board
E-Number (Finland)	3707569
E-Number (Norway)	4190241
E-Number (Sweden)	3210558
ETIM 8	EC001653 - Installation contactor for distribution board

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
1SAE901901R1011	EH04-11N Auxiliary Contact - 0 NO - 0 NC - Auxiliary Circuit 50 Hz	EH04-11N	1	piece
1SAE901901M1011	EH04-11N Auxiliary Contact - 0 NO - 0 NC - Auxiliary Circuit 50 Hz	EH04-11N	1	piece
1SAE901901R1020	EH04-20N Auxiliary Contact - 0 NO - 0 NC - Auxiliary Circuit 50 Hz	EH04-20N	1	piece
1SAE901901M1020	EH04-20N Auxiliary Contact - 0 NO - 0 NC - Auxiliary Circuit 50 Hz	EH04-20N	1	piece

分类

低压产品及系统 → 控制产品 → 接触器 → 建筑用接触器
低压产品及系统 → 线路保护产品 → Command and Signalling Devices → 建筑用接触器

