

cUL 1015 MTW 22 AWG PVC, 100m reel



Part NO: RGW-1626-5

Product Code: cUL PVC Hoop up Wire

Product Description

Application:

general application and according to customer

Multi-construction

Single

Construction

Single	Tinned copper
AWG	22
Construction	T0.25±0.008x7
Stranded Dia.(mm)	0.76
Jacket	PVC
Nom.Thickness	0.81
Jacket Dia.(mm)	2.39±0.15
Jacket Color	see table below

Marking(Color see table 1,3times/Per meters)(height:>=0.4mm)

Exxxxxx MTW 600V AWM STYLE 1015
105C 600V VW-1 22 AWG --- cUL TEW 105C 600V FT1 ROHS

PACKAGING

100m reel

ROHS Coppliance

RoHS GUIDELINE			
We operate according to the following standards			
Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS	/
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	/


Product label+UL label



Revision History

A0-1

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω /Km)	54.2
Rated Temperature(°C)	AWM/Style 1015 105
	CSA TEW 105
Rated Voltage(V)	600
20°C Insulation Resistance(M Ω .KM)	> 200

Part Number	Colour
#2105	Black
#2106	White
#2107	Blue
#2108	Red
#2109	Green

Product label

22 AWG (7/30)TC (0.81mm) PVC INS
UL MTW 90C DRY/60C WET/600V or
AWM STYLE 1015 105 C 600V CSA TEW
105C 600V FT1
USE: Internal wiring of appliances
where exposed to oil at temperature
not exceeding 60C

Date: 2012-07-04

Page : 1 of 1