



Product data sheet

Power tools for trade & industry

Line Laser

PRO GLL 80-33 G



Easier alignment with our intuitive line laser

The most important data

| | |
|-----------------------------|---------------|
| Working range with receiver | 80 m (radius) |
| Working range, value | 30 m |
| Accuracy | ± 0.3 mm/m |

Part Number 0 601 065 500

Technical data

Technical data

| | |
|-----------------------------|---|
| Battery voltage | 3.7 V |
| Laser diode | 500 – 540 nm, < 10 mW |
| Operating temperature | -10 – 40 °C |
| Storage temperature | -20 – 70 °C |
| Laser class | 2 |
| Working range, value | 30 m |
| Working range with receiver | 80 m (radius) |
| Accuracy | ± 0.3 mm/m |
| Self-levelling range | ± 4° |
| Levelling time | 4 s |
| Dust and splash protection | IP 65 |
| Power supply | 4 x 1.5 V LR6 (AA), 3.7 V Li-Ion battery (3000 mAh) |
| Operating time (max.) | 5 h (Li-Ion) and 5 h (4 x AA) in 3-line mode |
| Tripod thread | 1/4", 5/8" |
| Weight, approx. | 0.93 kg |
| Colour of laser line | green |
| Projection | 3 x 360° line |
| Compatible laser receivers | LR 7 |



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Rubber-enforced housing and IP65 rating for dust and water resistance
- New keypad design for clear laser line selection and energy saving mode for longer battery runtime
- Dual power source for seamless switch between BA 3.7V 3.0Ah XL Li-Ion battery and AA alkaline batteries to help eliminate downtime



PROTECTED TOOLS
Impact | Water | Dust



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

