

## Main

Range of product	TeSys GS 250...400
Device short name	Auxiliary blown fuse contact
Product or component type	Auxiliary contact
Product compatibility	GS 250 A Size 1 GS 400 A Size 2
Poles description	3P
[Ie] rated operational current	0.6 A at 110 V DC-13 0.4 A at 220 V DC-13 4 A at 230 V AC-15 3 A at 400 V AC-15 2 A at 48 V DC-13 12 A at 24 V DC-13

## Complementary

Fuse type	BS DIN NFC
Fuse size	T1 T2
Contacts type and composition	1 NO/NC
Product weight	0.038 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.