

Specifications

Eaton 160LMT

Eaton Bussmann series high speed British standard fuse, Single barrel, 160A, 240 VAC/150 VDC (IEC), 250 VAC/150 VDC (UL), Class aR, Breaking capacity 200 kA RMS Sym., 40 kA DC at 150 VDC (IEC). 50 kA at 150 VDC (UL)

General specifications

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	160LMT
EAN	5027590035347
UPC	051712831604
PRODUCT LENGTH/DEPTH	84 mm
PRODUCT HEIGHT	41 mm
PRODUCT WIDTH	39 mm
PRODUCT WEIGHT	180 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated Designed and tested to BS88 part 4 UL recognized IEC 60269-4 CCC

Electrical data

AMPERAGE RATING	160 A
VOLTAGE RATING	240 Vac, 150 Vdc
RATED VOLTAGE AC	240 V
RATED VOLTAGE DC	150 V
INTERRUPT RATING	200 kA RMS Sym, 40 kA at 150 Vdc (IEC) 200 kA RMS Sym, 50 kA at 150 Vdc (UL)
CLASS	Class aR
PRE ARC (I2T)	1100
CLEARING (I2T)	16000
WATT LOSSES	17 W

Compatible Trip indicator/Microswitch

SUITABLE FOR	MC-250 Trip indicator kit (indicator + clips) TI250 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
---------------------	---

Product specifications

APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE INDICATOR	None

Resources

BROCHURES	eaton-bussmann-series-bs88-high-speed-fuses-product-aid-pa135003en-us.pdf
CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf
DECLARATIONS OF CONFORMITY	eaton-high-speed-british-standard-fuse-declaration-of-conformity-eu250045en.pdf eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250923en.pdf
MCAD MODEL	eaton-hs-bs88-body-fuses-mcad-3d-models-160-450a-lmt.stp
TECHNICAL DATA SHEETS	720004 LCT, LET, LMMT, LMT

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

