



Due to its wide operating voltage and automatic synchronisation, the Solex beacon is a flexible solution for all types of alarm and monitoring systems.

Powered by Xenon technology, the Solex is a cost effective solution that can complement audible alarms in high-noise environments.


### Features

- 3 light output options
- 5 lens colour options
- 9-60V
- Tamper switch option

### Benefits

- Manage the current to suit your application
- Use for fire warning or general signalling
- Wide operating voltage for maximum flexibility
- For use where security is an issue (tamper switch)

### Dimensions



### Technical Specification

<b>Voltage</b>	9 - 60Vdc
<b>Current</b>	3 / 5 / 15mA (user selectable)
<b>Light Output</b>	0.5 / 1 / 3cd (user selectable)
<b>Flash Rate</b>	Single flash @ 1Hz Double flash @ 1Hz Continuous (user selectable)
<b>Monitoring</b>	Reverse polarity
<b>Temperature</b>	- 10°C to + 55°C
<b>Protection</b>	IP21C (s)* IP65 (d)*
<b>Construction</b>	Base ABS, FR, PC lens
<b>Weight</b>	0.1Kg
<b>Colour</b>	Red or white
<b>Flash colour</b>	Red, amber, blue, green or white

(s)\* Shallow Base

(d)\* Deep / U Base

Solex Amber - White Base



### Catalogue Numbers

Reference	Cat No	Description
SO/R/SR/3C	531025FULL-0061	Solex Beacon, Red Lens, Red Body, Shallow Base, 3cd
SO/R/DR/3C	531025FULL-0087	Solex Beacon, Red Lens, Red Body, Deep Base, 3cd
SO/R/SR/10C	531024FULL-0060	Solex Beacon, Red Lens, Red Body, Shallow Base, 10cd
SO/R/DR/10C	531024FULL-0088	Solex Beacon, Red Lens, Red Body, Deep Base, 10cd
SO/R/SR/15C	531028FULL-0064	Solex Beacon, Red Lens, Red Body, Shallow Base, 15cd
SO/R/DR/15C	531028FULL-0111	Solex Beacon, Red Lens, Red Body, Deep Base, 15cd

For full list of part numbers, turn to page 79

