



ENGLISH

Datasheet

RS 100m PE Insulated, Shielded Single Core Microphone Cable, PVC Sheath, 3.1mm OD 100m RS Stock No. 748-1958



Product Description

Application:

For Microphone Cable

Multi-construction

1 Core

Construction


1 Core	Tinned Copper
Construction	T0.2±0.008×7
Stranded Dia.(mm)	0.60
Insulation 1	PE
Thickness	0.25
Insulation Dia.(mm)	1.1±0.08
Insulation Color	Natrual
Drain Wire	Tinned Copper
Construction(mm)	T0.2±0.008×7
Insulation 2	Simi-Conductive PE
Thickness	0.25
Insulation Dia.(mm)	2.2±0.15
Insulation Color	Black
Jacket	PVC
Thickness(mm)	0.40
Dia.(±0.1mm)	3.10
Jacket Color	Black

Marking(white ink; once/meter)

1 Core Microphone Cable PVC [Weekyear] [Metermark]

PACKAGING

100M/Reel

Design**Electrical Characteristics**

Max.Conductor DC Resistance at 20 °C (Ω /Km)	<92
Rated Temperature(°C)	-20~70
Rated Voltage (V)	60
Min.Insulation DC Resistance at 20 °C (M Ω *Km)	>200