

Specifications



Photo is representative

Eaton 242470

Eaton Moeller series xPole - PLS6/M MCB.
PLSM, 3-pole, tripping characteristic: C,
rated current I_n : 10 A, rated switching
capacity IEC/EN 60898-1: 10 kA

General specifications

PRODUCT NAME	Eaton Moeller series xPole - PLS6/M MCB
CATALOG NUMBER	242470
MODEL CODE	PLSM-C10/3-MW
EAN	4015082424701
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	52.5 mm
PRODUCT WEIGHT	0.314 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

Delivery program

APPLICATION

- Switchgear for residential and commercial applications
- xPole - Switchgear for residential and commercial applications

NUMBER OF POLES	Three-pole
-----------------	------------

NUMBER OF POLES (TOTAL)	3
-------------------------	---

NUMBER OF POLES (PROTECTED)	3
-----------------------------	---

TRIPPING CHARACTERISTIC	C
-------------------------	---

RELEASE CHARACTERISTIC	C
------------------------	---

AMPERAGE RATING	10 A
-----------------	------

TYPE

- Miniature circuit breaker
- PLSM

Technical data - electrical

VOLTAGE TYPE	AC
--------------	----

RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
--------------------------------------	-------

RATED INSULATION VOLTAGE (UI)	440 V
-------------------------------	-------

RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
--	------

FREQUENCY RATING - MIN	50 Hz
------------------------	-------

FREQUENCY RATING - MAX	60 Hz
------------------------	-------

RATED SWITCHING CAPACITY (IEC/EN 60898-1)	10 kA
---	-------

RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60898) AT 230 V	10 kA
---	-------

RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60898) AT 400 V	10 kA
---	-------

RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2) AT 230 V	0 kA
--	------

RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2) AT 400 V	0 kA
--	------

OVERVOLTAGE CATEGORY	III
----------------------	-----

POLLUTION DEGREE	2
------------------	---

Technical data - mechanical

WIDTH IN NUMBER OF MODULAR SPACINGS	3
--	---

BUILT-IN DEPTH	70.5 mm
-----------------------	---------

DEGREE OF PROTECTION	IP20
-----------------------------	------

CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
---	-------------------

CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
---	--------------------

CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
--	-------------------

CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
--	--------------------

Design verification as per IEC/EN 61439 - technical data

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	10 A
--	------

HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
---	-----

EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	4.6 W
--	-------

STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
---	-----

HEAT DISSIPATION CAPACITY	0 W
----------------------------------	-----

AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
--	--------

AMBIENT OPERATING TEMPERATURE - MAX	75 °C
--	-------

Design verification as per IEC/EN 61439

10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF	Is the panel builder's responsibility.

Additional information

CURRENT LIMITING CLASS	3
FEATURES	Additional equipment possible
SPECIAL FEATURES	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
USED WITH	Miniature circuit breaker PLSM

INSULATING MATERIAL

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

CATALOGUES	eaton-xpole-protective-devices-catalog-ca019014en-en-us.pdf
	eaton-xpole-plsm-mcb-catalog-ca019064en-en-us.pdf
	eaton-xpole-pls6-mcb-catalog-ca019065en-en-us.pdf
CHARACTERISTIC CURVE	eaton-xpole-mmc4-6-m-mcb-characteristic-curve-002.jpg
DECLARATIONS OF CONFORMITY	eaton-mcb-declaration-of-conformity-eu250405en.pdf
DRAWINGS	eaton-xpole-mmc4-6-m-mcb-dimensions.jpg
	eaton-xpole-mmc4-6-m-mcb-3d-drawing-007.jpg
ECAD MODEL	ETN.PLSM-C10_3-MW.edz
INSTALLATION INSTRUCTIONS	eaton-rccb-rcbo-g9-il019140zu.pdf
MCAD MODEL	pls_3p.dwg pls_3p.stp
PEP ECO-PASSPORT	EATO-00046-V01.01-EN
WIRING DIAGRAMS	eaton-xpole-mmc4-6-m-mcb-wiring-diagram-005.jpg

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

