




Connectors > Socket Connectors > IC Sockets > DIP Sockets



Number of Positions: **96**

Connector Profile: **Standard**

Row-to-Row Spacing: **2.54 mm [.1 in]**

Contact Current Rating (Max): **1.5 A**

Features

Configuration Features

PCB Mount Orientation	Vertical
Number of Rows	3
Number of Positions	96

Body Features

Frame Style	Open
Connector Profile	Standard

Contact Features

Contact Base Material	Phosphor Bronze
Contact Type	Pin
Contact Current Rating (Max)	1.5 A

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With

Housing Features

Housing Material	Polyester GF
------------------	--------------

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Product Length	93.7 mm[3.689 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
Packaging Quantity	300

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #2-87456-9
34 MODIV HSG COMP DR .100CL



TE Part #3-87456-6
40 MODIV HSG DR MRKD .100CL



TE Part #102107-2
MOD IV PIN LP



TE Part #1-641737-1
04P CMNL HDR ASSY R/A V0



TE Part #750644-1
50SR SCREWLOCK KIT,FEMALE




TE Part #2-1879027-3
YR1 0.1% 806K



TE Part #6-1879662-9
H8 51R1 0.1% 15PPM



TE Part #2176055-1
RLP73V 2B R010 1% 1K RL



TE Part #CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS

Documents

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_166467-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_166467-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_166467-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

