

## Datasheet

# 95 Industrial Grade Mechanics Tool Kit

RS Stock number [604-781](#)



### Description:

A high quality mechanic's/fitter's tool kit comprising 95 industrial grade tools in an 18 in cantilever steel tool box. The tool box is of a strong hinged and riveted construction and comprises 4 trays, 422'95'47 each (1 of which is sub-divided), and a large base storage area, 422'200'103. It is lockable (padlock supplied) and has a tubular steel carrying handle.



**Kit Contents:**

Flared tip screwdrivers 4'1/4 in. 6'5/16 in. 10'3/8 in.	sliding 'T' handle Hexagon keys: A/F (mm) 1.5, 2, 2.5, 3, 4, 5, 6, 7 & A/F
Parallel tip screwdrivers 4' 1/8 in. & 6' 3/16 in.	(imperial) 1/16, 5/64 3/32, 1/8, 5/32, 3/16, 7/32, 1/4
Supadriv/Pozidriv™ No.1 and No.2 screwdrivers	Junior hacksaw & blade
Supadriv/Pozidriv™ No. 2 chubby screwdriver	Tin snips
Flared tip chubby screwdriver	Pin punches: 2, 3, 4 mm dia.
8 in. combination pliers	Centre punch
7 in. radio pliers	1 lb ball pein hammer
6 1/2 in. diagonal cutters	1 lb soft faced hammer
9 1/2 in. utility pliers	16 & 22 mm cut cold chisels Internal/external interchangeable tip circlip plier
10 in. self-grip wrench	Safety spectacles
8 in. adjustable spanner	8 in. hand file, 8 in. half round file, 8 in. round file & Magneto file
Combination spanners: 8 to 19mm A/F and 7/16 to in. A/F	3 m/10 ft measuring tape
Open ended spanners: 5'6, 5.5'7, 8'10mm & BA 10'8, 4'6, 0'2	12 in./300 mm steel rule
3/8in square drive socket set: 10 to 22mm (7/16 to 1 1/16)	Metric & imperial feeler gauges
10 in. ratchet handle, 5 in. & 10 in. extension	Padlock