




---

 PRODUCT-DETAILS

# OT60FT3

## OT60FT3 SWITCH-DISCONNECTOR




---

**General Information**

Extended Product Type	OT60FT3
Product ID	1SCA105081R1001
EAN	6417019392110
Catalog Description	OT60FT3 SWITCH-DISCONNECTOR
Long Description	3-pole, front operated, door mounted, switch-diconnector / non-fusible diconnect switch with front protected clamp terminals, handle and shaft are not included

---

**ABB EcoSolutions**

Environmental Product Declaration - EPD	1SCC301280D0201
---	-----------------

---

**Material Compliance**

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201

RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

## Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301060M0004
Mechanical Drawings	1SCC301470F0001 1SCC301469F0001 OT125FT3.igs
Environmental Product Declaration - EPD	1SCC301280D0201

## Environmental

Degree of Protection	Front IP20
Pollution Degree	3

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

## Dimensions

Product Net Width	70 mm
Product Net Height	100 mm
Product Net Depth / Length	66.5 mm
Product Net Weight	0.42 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	102 mm
Package Level 1 Depth / Length	71 mm
Package Level 1 Height	76 mm
Package Level 1 Gross Weight	0.44 kg
Package Level 1 EAN	6417019392110

## Technical

Cable Cross-Section	Cu 2.5 ... 25 mm <sup>2</sup>
Connecting Capacity Main Circuit	Flexible 1x Cu 2.5...25 mm <sup>2</sup> Stranded 1x Cu 2.5...25 mm <sup>2</sup>

Degree of Protection	Front IP20
Handle Type	Handle and shaft not included
Mechanical Durability	20000
Mounting Type	Door mounting
Number of Poles	3P
Operating Mode	Front
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 1.6 W
Rated Impulse Withstand Voltage ( $U_{imp}$ )	8 kV
Rated Insulation Voltage ( $U_i$ )	acc. to IEC/EN 60664-1 750 V
Rated Operational Current AC-22A ( $I_e$ )	(380 ... 415 V) 63 A (500 V) 63 A (690 V) 63 A
Rated Operational Current AC-23A ( $I_e$ )	(380 ... 415 V) 63 A (500 V) 63 A (690 V) 40 A
Rated Operational Power AC-23A ( $P_e$ )	(380 ... 415 V) 37 kW (500 V) 37 kW (690 V) 37 kW
Rated Operational Voltage	Main Circuit 750 V
Rated Short-Circuit Making Capacity ( $I_{cm}$ )	(690 V) 3.6 kA
Rated Short-time Withstand Current Low Voltage ( $I_{cw}$ )	for 1 s 2.5 kA
Recommended Screw Driver	Main Circuit Hexagon 4
Special Functions	No
Standards	IEC 60947-3 / UL 98 / CSA C22.2 NO.4
Terminal Type	Screw Terminals
Tightening Torque	acc. IEC 60947-1 6.2 N·m
Wire Stripping Length	Main Circuit 17-18 mm

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	600 V
Ampere Rating	60 A
Horsepower Rating UL/CSA	(110 ... 120 V AC) Single Phase 3 Hp (240 V AC) Single Phase 7.5 Hp (220 ... 240 V AC) Three Phase 20 Hp (440 ... 480 V AC) Three Phase 40 Hp (550 ... 600 V AC) Three Phase 40 Hp
Wire Stripping Length	Main Circuit 17-18 mm
Recommended Screw Driver	Main Circuit Hexagon 4
Tightening Torque	acc. IEC 60947-1 6.2 N·m

## Certificates and Declarations

A2L Certificate – IEC	1SCC301335D0201
ATEX Certificate	No certification needed
Declaration of Conformity - CE	1SCC301010D0201

UL Certificate	cULus certificate OT30-125
VDE Certificate	No certification needed

---

## External Classifications and Standards

---

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122233
IDEA Granular Category Code (IGCC)	5290 >> Disconnect switch
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

## Categories

---

Low Voltage Products and Systems → Switches → Switch Disconnectors

