



2 YEARS
MANUFACTURER
GUARANTEE



Product number

1506321

EAN

3281855063212

DESCRIPTION

- Extra large display for weekdays, hours in 12 and 24 hour format, minutes and seconds as well as mode.
- Activatable background lighting for easy readability.
- 10 ON/OFF programmes for day, hour and minute setting.
- Easy to use.
- Shortest switching-time 1 minute.
- Countdown function.
- Random function.
- Summer/Winter time.
- Manual ON/OFF.
- Programme: Interruption during operation is possible.
- Data memory in case of power cut.
- Includes NiMH rechargeable batterie.
- Socket with increased touch protection.

TECHNICAL DATA

Number of batteries	1
Battery type	Built-in battery pack
Battery technology	Nickel metal hydride

Max. current carrying capacity	16 A
Degree of protection (IP)	IP20
Colour	White

PACKAGING, DIMENSIONS AND WEIGHTS

Packaging	In display packaging
UP	1
Weight of product (without packaging)	0.16 kg

Dimension LxWxH (without packing)	7.6 cm x 5.9 cm x 12.3 cm
Weight of product (including packaging)	0.22 kg
Dimension LxWxH (incl. packing)	8.5 cm x 7 cm x 17.5 cm