

pendant station XAC-D - 1 rocker lever 1 Emergency stop

XACD24A1241

EAN Code: 3389110166118

Main

Range of product	Harmony XAC	
Product or component type	Pendant control station	
Device short name	XACD	

Complementary

Control station type	Double insulated			
Enclosure material	Polypropylene			
control type	Intuitive			
Electrical circuit type	Control circuit			
Enclosure type	Complete ready for use			
Control station application	Control of 2-speed hoist motor			
Motor starter type	Reversing			
Control station composition	1 2-directional button + 1 emergency stop			
Control button type	Emergency stop push-button Ø 30 mm 1 NC trigger action First direction button 1 NC + 2 NO raise, slow-fast Second direction button 1 NC + 2 NO lower, slow-fast			
Product compatibility	ZB2BE102 for emergency stop XEDS1241 for reversing operation			
Mechanical interlocking	With mechanical interlocking			
Control station colour	Yellow			
Connections - terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end			
Standards	UL 508 EN/IEC 60947-5-5 EN/IEC 60204-32 EN/ISO 13850: 2006 EN/IEC 60947-5-1 CSA C22.2 No 14			
Protective treatment	тн			
Ambient air temperature for operation	-2570 °C			
Ambient air temperature for storage	-4070 °C			
Vibration resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6			
Shock resistance	70 gn conforming to IEC 60068-2-27			
Overvoltage category	Class II conforming to IEC 61140			
IP degree of protection	IP65 conforming to IEC 60529			

IK degree of protection	IK08 conforming to EN 50102 3000000 cycles		
Mechanical durability			
Cable entry	Rubber sleeve with stepped entry 718 mm		
Contact code designation	A600 AC-15, Ue = 240 V, Ie = 3 A conforming to IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A conforming to IEC 60947-5-1 appendix A		
[Ithe] conventional enclosed thermal current	16 A		
[Ui] rated insulation voltage	600 V (pollution degree 3) conforming to IEC 60947-1		
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-1		
Contact operation	Staggered Snap action		
Maximum resistance across terminals	25 MOhm		
Operating force	16 N		
Short-circuit protection	10 A fuse protection by cartridge fuse type gG		
Rated operational power in W	40 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 120 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C 48 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 48 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C 65 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 24 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C		
Terminals description ISO n°1	(23-24)NO_CL (61-62)NC (13-14)NO (33-34)NO (43-44)NO_CL (51-52)NC		
Terminals description ISO n°2	(11-12)NC		
Terminal identifier	(11-12)NC (13-14)NO		
Product weight	0.42 kg		

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9 cm
Package 1 Width	12.5 cm
Package 1 Length	31.5 cm
Package 1 Weight	549 g
Unit Type of Package 2	S02
Number of Units in Package 2	3
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	1.933 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty

1 Jul 2025

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

Q	Environmental footprint
---	-------------------------

Environmental Disclosure

Product Environmental Profile

Use Better


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture			
Circularity Profile	No need of specific recycling operations		
Take-back	No		
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		

Dimensions Drawings

Dimensions



- (1) With trigger action latching Ø 30 mm / 1.18 in. Emergency stop.
- (2) Internal Ø


XACD24A1241

Performance Curves

Rated Operational Power

AC Supply 50/60 Hz Inductive Circuit

Operating rate: 3600 operating cycles/hour. Load factor: 0.5. Millions of operating cycles, AC-15 utilization category



Ithe Thermal current

(A) Current

DC Supply

Operating rate: 3600 operating cycles/hour. Load factor: 0.5.

Power broken in W for 1 million operating cycles, DC-13 utilization category

Voltage	V	24	48	120
Inductive circuit	w	65	48	40