




Photoelectric angle sensor

OPL-DPKG/US



Product characteristics

Type of light	red light
---------------	-----------

Application

Special feature	Function check output
-----------------	-----------------------

Electrical data

Operating voltage	[V]	10...35 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 45
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2
Function check output		yes
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	200



Photoelectric angle sensor

OPL-DPKG/US

Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Operating conditions

Ambient temperature	[°C]	-10...60
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
MTTF	[years]	919

Mechanical data

Weight	[g]	150
Dimensions	[mm]	65 x 10 x 106
Side length X	[mm]	54
Side length Y	[mm]	55
Sensor width Z	[mm]	60.46
Materials		housing: diecast zinc; lens: glass

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, yellow

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection


Connector: 1 x M12; coding: A



Photoelectric angle sensor

OPL-DPKG/US

Connection



2

Function check output