Product datasheet

Specifications



auxiliary contact - 1 NC + 1 OC - 380..415 V - 6 A - for RCCB

16940

EAN Code: 3303430169406

Main

range of product	Multi9
Product or component type	OC contact
Device short name	OFSP
Signal contacts composition	1 C/O 1 NC
[In] rated current	AC-12 3 A at 380...415 V, AC 50/60 Hz AC-12 6 A at 220...240 V, AC 50/60 Hz DC-12 1 A at 130 V, DC DC-12 1.5 A at 60 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC
Standards	EN/IEC 60947-5-1

Complementary

mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	NO
Connections - terminals	Tunnel type terminal: 2 cable(s) 1…1.5 mm² - flexible Tunnel type terminal: 2 cable(s) 1…1.5 mm² - rigid
Tightening torque	0.8 N.m

Environment

IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Ambient air temperature for operation	-25…50 °C
Ambient air temperature for storage	-40…85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.700 cm
Package 1 Width	8.100 cm
Package 1 Length	9.500 cm
Package 1 Weight	52.000 g
Unit Type of Package 2	S02

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 2	45
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.486 kg

Logistical informations

Country of origin	DE

Contractual warranty

Warranty (in months)	18

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
SCIP Number	9da5f8d9-d60f-424a-bb30-a856a097686c
EU RoHS Directive	Compliant By Exemption
REACh Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension

Repair	No

Use Again

Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins