

**FAG****7320-B-XL-TVP** [↗](#)

Angular contact ball bearing

Angular contact ball bearing 73...-B-XL-TVP,  
single row, X-life, plastic cage**X-life**

## Technical information



## Your current product variant

Design variant	B	B
Sealing	Without	Not sealed
Cage	TVP	solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased

## Main Dimensions &amp; Performance Data

d	100 mm	Bore diameter
D	215 mm	Outside diameter
B	47 mm	Width
C <sub>r</sub>	214,000 N	Basic dynamic load rating, radial
C <sub>0r</sub>	197,000 N	Basic static load rating, radial
C <sub>ur</sub>	10,900 N	Fatigue load limit, radial
n <sub>G</sub>	4,050 1/min	Limiting speed
n <sub>gr</sub>	3,550 1/min	Reference speed
≈m	7.14 kg	Weight



Mounting dimensions

$d_{a\ min}$	114 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	201 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	208 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2.5 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	1 mm	Maximum fillet radius of housing






Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
$r_{1\ min}$	1.1 mm	Minimum chamfer dimension
$D_1$	171.72 mm	Shoulder diameter on outer ring wide side face
$d_1$	146.26 mm	Shoulder diameter on inner ring wide side face
$a$	89.6 mm	Distance between the apexes of the pressure cones
$\alpha$	40 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Characteristics

-   $F_r$  Radial load
-   $F_a$  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed