




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 28

Primary Product Color: Black

Protection & Strain Relief Accessory Type: Cover - Cable Exit

Primary Product Material: PBT GF

Strain Relief: Without

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover - Cable Exit
---	--------------------

Configuration Features

Number of Positions	28
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF

Mechanical Attachment

Strain Relief	Without
---------------	---------

Dimensions

Compatible Cable Bundle Diameter Range	10.75 mm[.423 in]
--	-------------------

Usage Conditions

Operating Temperature (Max)	140 °C[284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Box
Packaging Quantity	1440



Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1393436-2
[V23542C1028B102=28P KABELBAUMS](#)



TE Part # 1411065-1
[ERSATZT-PACK F28P](#)

Also in the Series | Timer Connector System



Automotive Connector Locks & Position Assurance(15)




Automotive Headers(19)



Automotive Housings(195)



Connector Seals & Cavity Plugs(36)




Crimp Terminal Housings(13)



Insertion & Extraction Tools(18)




Other Automotive Connector Accessories(1)



PCB Headers & Receptacles(19)




Rectangular Power Connectors(2)



Wire-to-Board Headers & Receptacles (19)

Customers Also Bought



TE Part #5-1534116-1
MQS0,63 SN REC CB UNSEAL. 0,25-0,35 2P



TE Part #969044-1
SPT A REC 6.3 Contact SWS Sn



TE Part #CH03686001
RBK-ILS-125-NR4-0-60MM




TE Part #1393450-3
V23542C1052B102=52P KABELBAUM-



TE Part #928911-2
RINGZUNGE MIF




TE Part #1393436-2
V23542C1028B102=28P KABELBAUMS



TE Part #1355044-1
STD POW TIM GEH 4P



TE Part #1813112-1
MCP 1.5&2.8 HYB 28P PLUG ASS'Y



Documents

Product Drawings

V23542C1028Z100=28P ABDECKKAPP

English

V23542C1028Z100=28P ABDECKKAPP

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1393454-1_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_1393454-1_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_1393454-1_A1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

product-1393454-1_datasheet

English