

Safety Data Sheet

FEROX CONVERTIRUGGINE



Safety Data Sheet dated 17/9/2021, version 8

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Mixture identification:

Trade name: FEROX CONVERTIRUGGINE

Trade code: 4145

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use:

Rust converter

1.3. Details of the supplier of the safety data sheet

Supplier:

Arexons S.p.A.

via Antica di Cassano, 23, 20063

Cernusco sul Naviglio (MI), Italy

Arexons S.p.A.

Tel. +39 (0)2/924361 - Fax +39 (0)2/92436306

Competent person responsible for the safety data sheet:

arexons@arexons.it

1.4. Emergency telephone number

Arexons S.p.A.

Tel. +39 (0)2/924361 - Fax +39 (0)2/92436306

In England and Wales: NHS 111 - dial 111

In Scotland: NHS 24 - dial 111

In Ireland: Beaumont Hospital - National Poisons Information Centre 01 809 2166 (7days, 8:00 - 22:00)

In South Africa: Poison Information Helpline 0861 555 777

In Malta: emergency number 112

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

EC regulation criteria 1272/2008 (CLP):

⚠ Warning, Skin Irrit. 2, Causes skin irritation.

⚠ Warning, Eye Irrit. 2, Causes serious eye irritation.

Adverse physicochemical, human health and environmental effects:

No other hazards

2.2. Label elements

Hazard pictograms:



Warning

Hazard statements:

H315 Causes skin irritation.

H319 Causes serious eye irritation.

Precautionary statements:

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

P103 Read carefully and follow all instructions.

P264 Wash hands thoroughly after handling.

P280 Wear protective gloves and eye/face protection.

Safety Data Sheet

FEROX CONVERTIRUGGINE



P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

Special Provisions:

None

Special provisions according to Annex XVII of REACH and subsequent amendments:

None

2.3. Other hazards

No PBT, vPvB or endocrine disruptor substances present in concentration $\geq 0.1\%$

Other Hazards:

No other hazards

SECTION 3: Composition/information on ingredients

3.1. Substances

N.A.

3.2. Mixtures

Hazardous components within the meaning of the CLP regulation and related classification:

$\geq 50\%$ - $< 60\%$ Vinyl acrylic copolymer emulsion

⚠ 3.2/2 Skin Irrit. 2 H315

⚠ 3.3/2 Eye Irrit. 2 H319

$\geq 0.05\%$ - $< 0.1\%$ and isobutane

REACH No.: 01-2119485395-27, Index number: 601-004-00-0, CAS: 75-28-5, EC: 200-857-2

⚠ 2.2/1A Flam. Gas 1A H220

⚠ 2.5/C Press Gas (Comp.) H280

SECTION 4: First aid measures

4.1. Description of first aid measures

In case of skin contact:

Immediately take off all contaminated clothing.

Areas of the body that have - or are only even suspected of having - come into contact with the product must be rinsed immediately with plenty of running water and possibly with soap.

Wash thoroughly the body (shower or bath).

Remove contaminated clothing immediately and dispose off safely.

After contact with skin, wash immediately with soap and plenty of water.

In case of eyes contact:

After contact with the eyes, rinse with water with the eyelids open for a sufficient length of time, then consult an ophthalmologist immediately.

Protect uninjured eye.

In case of Ingestion:

Do not under any circumstances induce vomiting. OBTAIN A MEDICAL EXAMINATION IMMEDIATELY.

In case of Inhalation:

Remove casualty to fresh air and keep warm and at rest.

4.2. Most important symptoms and effects, both acute and delayed

None

4.3. Indication of any immediate medical attention and special treatment needed

In case of accident or unwellness, seek medical advice immediately (show directions for use or

Safety Data Sheet

FEROX CONVERTIRUGGINE



safety data sheet if possible).

Treatment:

None

SECTION 5: Firefighting measures

5.1. Extinguishing media

Appropriate Extinguishing Media:

To carbon dioxide.

To dust.

Foam

Water spray.

Not Recommended Extinguishing Media:

Do not use direct water jets.

5.2. Special hazards arising from the substance or mixture

Do not inhale explosion and combustion gases.

Burning produces heavy smoke.

5.3. Advice for firefighters

Use suitable breathing apparatus .

Collect contaminated fire extinguishing water separately. This must not be discharged into drains.

Move undamaged containers from immediate hazard area if it can be done safely.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear personal protection equipment.

Remove persons to safety.

See protective measures under point 7 and 8.

6.2. Environmental precautions

Do not allow to enter into soil/subsoil. Do not allow to enter into surface water or drains.

Retain contaminated washing water and dispose it.

In case of gas escape or of entry into waterways, soil or drains, inform the responsible authorities.

Suitable material for taking up: absorbing material, organic, sand

6.3. Methods and material for containment and cleaning up

Wash with plenty of water.

6.4. Reference to other sections

See also section 8 and 13

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid contact with skin and eyes, inhalation of vapours and mists.

Don't use empty container before they have been cleaned.

Before making transfer operations, assure that there aren't any incompatible material residuals in the containers.

See also section 8 for recommended protective equipment.

Advice on general occupational hygiene:

Contaminated clothing should be changed before entering eating areas.

Do not eat or drink while working.

7.2. Conditions for safe storage, including any incompatibilities

Keep away from food, drink and feed.

None in particular.

Instructions as regards storage premises:

Adequately ventilated premises.

7.3. Specific end use(s)

None in particular

Safety Data Sheet

FEROX CONVERTIRUGGINE



SECTION 8: Exposure controls/personal protection

- 8.1. Control parameters
and isobutane - CAS: 75-28-5
ACGIH - STEL: 1000 ppm - Notes: (EX) - CNS impair
VLE short - 1000 ppm
DNEL Exposure Limit Values
N.A.
PNEC Exposure Limit Values
N.A.
- 8.2. Exposure controls
Eye protection:
Eye glasses with side protection.
Compliant with EN 166
Protection for skin:
protective clothing
Protection for hands:
Nitrile or Viton gloves.
Compliant with EN 374.
Respiratory protection:
Not needed for normal use.
Thermal Hazards:
None
Environmental exposure controls:
None
Appropriate engineering controls:
None

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Properties	Value	Method:	Notes:
Physical state:	Liquid	--	--
Colour:	ivory	--	--
Odour:	Characteristic	--	--
Melting point/freezing point:	N.A.	--	--
Boiling point or initial boiling point and boiling range:	100°C	--	--
Flammability:	N.A.	--	--
Lower and upper explosion limit:	N.A.	--	--
Flash point:	Not flammable	--	--
Auto-ignition temperature:	N.A.	--	--
Decomposition temperature:	N.A.	--	--
pH:	2.5	--	--

Safety Data Sheet

FEROX CONVERTIRUGGINE



Kinematic viscosity:	N.A.	--	--
Solubility in water:	Soluble	--	--
Solubility in oil:	N.A.	--	--
Partition coefficient n-octanol/water (log value):	N.A.	--	--
Vapour pressure:	N.A.	--	--
Density and/or relative density:	1.2 approx.	--	--
Relative vapour density:	N.A.	--	--
Particle characteristics:			
Particle size:	N.A.	--	--

9.2. Other information
No other relevant information

SECTION 10: Stability and reactivity

- 10.1. Reactivity
Stable under normal conditions
- 10.2. Chemical stability
Stable under normal conditions
- 10.3. Possibility of hazardous reactions
None
- 10.4. Conditions to avoid
Stable under normal conditions.
- 10.5. Incompatible materials
None in particular.
- 10.6. Hazardous decomposition products
None.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Toxicological information of the product:

FEROX CONVERTIRUGGINE ML 750

a) acute toxicity

Not classified

Based on available data, the classification criteria are not met

b) skin corrosion/irritation

The product is classified: Skin Irrit. 2 H315

Test: oecd 8 - Route: Skin - Species: RHE Negative 98 % - Duration: 3min - Notes: test condotto su formula analogo - Based on available data, the classification criteria are not met

Test: oecd 8 - Route: Skin - Species: RHE Negative 97.61 % - Duration: 1h - Notes: test condotto su formula analogo - Based on available data, the classification criteria are not met

c) serious eye damage/irritation

The product is classified: Eye Irrit. 2 H319

Safety Data Sheet

FEROX CONVERTIRUGGINE



Test: oecd 9 - Route: EYE - Species: BCOP Negative 11.58 - Notes: test condotto su formula analogo - Based on available data, the classification criteria are not met

Test: Eye Irritant - Route: EYE Positive

d) respiratory or skin sensitisation

Not classified

Based on available data, the classification criteria are not met

e) germ cell mutagenicity

Not classified

Based on available data, the classification criteria are not met

f) carcinogenicity

Not classified

Based on available data, the classification criteria are not met

g) reproductive toxicity

Not classified

Based on available data, the classification criteria are not met

h) STOT-single exposure

Not classified

Based on available data, the classification criteria are not met

i) STOT-repeated exposure

Not classified

Based on available data, the classification criteria are not met

j) aspiration hazard

Not classified

Based on available data, the classification criteria are not met

Toxicological information of the main substances found in the product:

N.A.

11.2. Information on other hazards

Endocrine disrupting properties:

No endocrine disruptor substances present in concentration $\geq 0.1\%$

SECTION 12: Ecological information

12.1. Toxicity

Adopt good working practices, so that the product is not released into the environment.

N.A.

12.2. Persistence and degradability

None

N.A.

12.3. Bioaccumulative potential

N.A.

12.4. Mobility in soil

N.A.

12.5. Results of PBT and vPvB assessment

vPvB Substances: None - PBT Substances: None

12.6. Endocrine disrupting properties

No endocrine disruptor substances present in concentration $\geq 0.1\%$

12.7. Other adverse effects

None

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Recover if possible. In so doing, comply with the local and national regulations currently in force.

Additional disposal information:

Reuse if possible. Act in accordance with the local and national laws in force.

CER 08 01 11 waste paint and varnish containing organic solvents or other dangerous substances.



SECTION 14: Transport information

14.1. UN number or ID number

Not classified as dangerous in the meaning of transport regulations.

14.2. UN proper shipping name

N.A.

14.3. Transport hazard class(es)

N.A.

14.4. Packing group

N.A.

14.5. Environmental hazards

ADR-Environmental Pollutant: No

IMDG-Marine pollutant: No

14.6. Special precautions for user

N.A.

14.7. Maritime transport in bulk according to IMO instruments

No

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Dir. 98/24/EC (Risks related to chemical agents at work)

Dir. 2000/39/EC (Occupational exposure limit values)

Regulation (EC) n. 1907/2006 (REACH)

Regulation (EC) n. 1272/2008 (CLP)

Regulation (EC) n. 790/2009 (ATP 1 CLP) and (EU) n. 758/2013

Regulation (EU) n. 2020/878

Regulation (EU) n. 286/2011 (ATP 2 CLP)

Regulation (EU) n. 618/2012 (ATP 3 CLP)

Regulation (EU) n. 487/2013 (ATP 4 CLP)

Regulation (EU) n. 944/2013 (ATP 5 CLP)

Regulation (EU) n. 605/2014 (ATP 6 CLP)

Regulation (EU) n. 2015/1221 (ATP 7 CLP)

Regulation (EU) n. 2016/918 (ATP 8 CLP)

Regulation (EU) n. 2016/1179 (ATP 9 CLP)

Regulation (EU) n. 2017/776 (ATP 10 CLP)

Regulation (EU) n. 2018/669 (ATP 11 CLP)

Regulation (EU) n. 2018/1480 (ATP 13 CLP)

Regulation (EU) n. 2019/521 (ATP 12 CLP)

Restrictions related to the product or the substances contained according to Annex XVII Regulation (EC) 1907/2006 (REACH) and subsequent modifications:

Restrictions related to the product:

Restriction 3

Restriction 40

Restrictions related to the substances contained:

No restriction.

Volatile Organic compounds - VOCs = 1.84 %

Volatile Organic compounds - VOCs = 18.36 g/Kg

Volatile Organic compounds - VOCs = 21.30 g/l

Where applicable, refer to the following regulatory provisions :

Directive 2012/18/EU (Seveso III)

Safety Data Sheet

FEROX CONVERTIRUGGINE



Regulation (EC) nr 648/2004 (detergents).
Dir. 2004/42/EC (VOC directive)

Provisions related to directive EU 2012/18 (Seveso III):
Seveso III category according to Annex 1, part 1
None

15.2. Chemical safety assessment
No Chemical Safety Assessment has been carried out for the mixture.
Substances for which a Chemical Safety Assessment has been carried out:
None

SECTION 16: Other information

Text of phrases referred to under heading 3:
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H220 Extremely flammable gas.
H280 Contains gas under pressure; may explode if heated.

Hazard class and hazard category	Code	Description
Flam. Gas 1A	2.2/1A	Flammable gas, Category 1A
Press Gas (Comp.)	2.5/C	Gases under pressure (Compressed gas)
Skin Irrit. 2	3.2/2	Skin irritation, Category 2
Eye Irrit. 2	3.3/2	Eye irritation, Category 2

This safety data sheet has been completely updated in compliance to Regulation 2020/878.
Classification and procedure used to derive the classification for mixtures according to Regulation (EC) 1272/2008 [CLP]:

Classification according to Regulation (EC) Nr. 1272/2008	Classification procedure
Skin Irrit. 2, H315	Calculation method
Eye Irrit. 2, H319	Calculation method

This document was prepared by a competent person who has received appropriate training.

Main bibliographic sources:

ECDIN - Environmental Chemicals Data and Information Network - Joint Research Centre,
Commission of the European Communities
SAX's DANGEROUS PROPERTIES OF INDUSTRIAL MATERIALS - Eight Edition - Van
Nostrand Reinold

The information contained herein is based on our state of knowledge at the above-specified date. It refers solely to the product indicated and constitutes no guarantee of particular quality.
It is the duty of the user to ensure that this information is appropriate and complete with respect to the specific use intended.

This MSDS cancels and replaces any preceding release.

ADR: European Agreement concerning the International Carriage of

Safety Data Sheet

FEROX CONVERTIRUGGINE



	Dangerous Goods by Road.
ATE:	Acute Toxicity Estimate
ATEmix:	Acute toxicity Estimate (Mixtures)
CAS:	Chemical Abstracts Service (division of the American Chemical Society).
CLP:	Classification, Labeling, Packaging.
DNEL:	Derived No Effect Level.
EINECS:	European Inventory of Existing Commercial Chemical Substances.
GefStoffVO:	Ordinance on Hazardous Substances, Germany.
GHS:	Globally Harmonized System of Classification and Labeling of Chemicals.
IATA:	International Air Transport Association.
IATA-DGR:	Dangerous Goods Regulation by the "International Air Transport Association" (IATA).
ICAO:	International Civil Aviation Organization.
ICAO-TI:	Technical Instructions by the "International Civil Aviation Organization" (ICAO).
IMDG:	International Maritime Code for Dangerous Goods.
INCI:	International Nomenclature of Cosmetic Ingredients.
KSt:	Explosion coefficient.
LC50:	Lethal concentration, for 50 percent of test population.
LD50:	Lethal dose, for 50 percent of test population.
NA:	Not applicable
PNEC:	Predicted No Effect Concentration.
RID:	Regulation Concerning the International Transport of Dangerous Goods by Rail.
STEL:	Short Term Exposure limit.
STOT:	Specific Target Organ Toxicity.
TLV:	Threshold Limiting Value.
TWA:	Time-weighted average
WGK:	German Water Hazard Class.