

CamCleaner 6000



Advantages

- Healthier employees
- Less cleaning
- Eliminates tobacco smoke, weld smoke, construction dust, asbestos and particles of all sizes down to ultrafine.
- Lower energy costs
- Reduced environmental impact
- Clean products, fewer operational disruptions
- Reduces the average temperature in rooms with high ceilings

Applications: Air purifier for dusty environments and large indoor premises such as pharmaceutical facilities, food factories, heavy industry, paper mills, welding workshops, timber facilities, bakeries, packaging production, printing facilities, stables, processing industry, supermarkets and other specialist applications such as upgrading of clean room environments and other classified assembly environments.

Power supply: 3-phase 380-480V or 1-phase 230V

Filter: F7, E11-H13

Fan: EC fan with adjustable airflow and ModBus connection.


Capacity: 0 - 6000 m³/h

Connection: 4 standard round (diameter 315mm) or 2 standard round (diameter 315mm) and 2 round (diameter 250mm) with sound reduction


Installation: Mobile or stationary, floor, wall or ceiling mounting (with wire or suspension arms).

Weight kg: 130,5 including filters

| Item no. | Type | Model | Dimensions (WxHxD) mm | Filter class compliant with EN1822 / EN779:2012 | Number of filters per air purifier |
|----------|-----------------------------------|------------|--------------------------|---|------------------------------------|
| 94000001 | CamCleaner 6000 230V, 1 phase | Vertical | 798x1968x820 | F7-E11 | 4 Pre + 2 Main |
| 94000002 | CamCleaner 6000 380-400V, 3 phase | Vertical | 798x1968x820 | F7-E11 | 4 Pre + 2 Main |
| 94000003 | CamCleaner 6000 230V, 1 phase | Horizontal | 1262x1359x829 | F7-E11 | 4 Pre + 2 Main |
| 94000004 | CamCleaner 6000 380-400V, 3 phase | Horizontal | 1262x1359x829 | F7-E11 | 4 Pre + 2 Main |



Air Cleaners



| Art. Nr | Item number | Item Name |
|-------------------------------|-------------|---|
| Upgrades | | |
| 94000008 | 1 | Upgrade prefilter to 97mm Ecopleat |
| 94000009 | 2 | Upgrade mainfilter to Hepa 13 |
| Accessories | | |
| 94000005 | 3 | Silencer (only for vertical model) |
| 94000010 | 4-5 | Ext. frame for Bagfilter/Citycarb/City-Flo size 592/592/ max 370-10-25 (delivered without filter) |
| 94000006 | 6 | Eyelets for ceiling mounting (Horizontal) |
| 94000007 | 7 | Constant airflow sensor |
| 94000015 | | UK Plug (1 Phase) |
| 94000016 | | UK Plug (3 phase) |
| 94000026 | 1 | Extension frame 97mm (Without filter) |
| 94000027 | 5 | Extension frame bag filter (Without filter) |
| 94000035 | 4 | Molecular box for 2X32 pcs CamCarb Green-R 1300 (Without molecular filter) |
| Exchange | | |
| | 8 | MGMM 11-1220X610X100-01 |
| | 9 | MGM 13-1220X610X100-01/10 |
| | 10 | Ecopleat F7-610X610X50mm |
| | 11 | Ecopleat F7-610X610X97mm |
| | | CamCarb Green-R 1300 |
| Other filter selection | | |
| | | Bagfilter XLT F7 592X592-max 380mm |
| | | CityCarb OPKCC-242412-M6-01PU 592x592x292 |
| | | City-Flo HFZS-F7-592/592/380-10-25 |

Air Cleaners

