

FlexiGuard Conduits & Fittings

FlexiGuard PVC Protective Conduits

FlexiGuard protective hoses are used to protect cables in machines and plant construction, and robotics as well as leads to switch cabinets.

Features and Benefits


- Extremely flexible
- Excellent mechanical protection
- Good resistance to oils, acids and alkalis
- Good resistance to chemicals
- Good resistance to UV and ozone



FlexiGuard FG with FG-UH fitting.

MATERIAL	Flexible Polyvinyl Chloride, cadmium free (PVC), Steel (ST)
Operating Temperature	-20 °C to +70 °C, (+80 °C, 200 h)
Flammability	UL94 HB

RoHS



FlexiGuard

TYPE	Ø D	Outside Ø (OD)	Min. Bending Radius (R)	Reel Length	Colour	Article-No.
FG14	10.0	14.0	14	10 m	Grey (GY)	167-00209
FG17	13.0	17.0	17	10 m	Grey (GY)	167-00211
FG19	15.0	19.0	19	10 m	Grey (GY)	167-00213
FG21	16.0	21.0	21	10 m	Grey (GY)	167-00216
FG27	21.0	27.0	27	10 m	Grey (GY)	167-00221
FG36	30.0	36.0	36	10 m	Grey (GY)	167-00229
FG45	38.0	45.0	45	10 m	Grey (GY)	167-00236
FG56	48.0	56.0	56	10 m	Grey (GY)	167-00248

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.