

L-ALEV 200K

Pressed steel swivel castor, medium duty design, with top plate fitting, heavy duty wheel, with 'Blickle EasyRoll' elastic solid rubber tyres, with aluminium wheel centre

EAN 4047526263546

ID 263541

Customs tariff number 87169090



Bracket: L series

- pressed steel, zinc-plated, blue-passivated, Cr6-free
- double ball bearing in the swivel head
- strong central kingpin (from wheel Ø 150 mm)
- swivel head seal
- minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process

Wheel: ALEV series

- tyre: high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A, colour black
- wheel centre: die-cast aluminium

Other features:

- high chemical resistance to many aggressive substances, except oils
- operating temperature: -20 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +60 °C

Technical data:

Wheel Ø (D)	☞	200 mm
Wheel width	⏏	50 mm
Load capacity at 4 km/h	⏏	400 kg
Load capacity (static)	⏏	1,000 kg
Bearing type	⦿	ball bearing
Total height (H)	⏏	235 mm
Mounting type		top plate
Plate size	⏏	140 x 110 mm
Bolt hole spacing	⏏	105 x 75–80 mm
Bolt hole Ø	⏏	11 mm
Offset (F)	⏏	65 mm
Temperature resistance min		-20 °C
Temperature resistance max		70 °C
Tread and tyre hardness		65 Shore A
Unit weight	⏏	3.1 kg
Non-marking		×
Non-staining		×
Antistatic	⏏	×
ESD		×
Electrically conductive	⏏	×
Corrosion-resistant		×
Heat-resistant	⏏	×
Suitable for autoclaves		×



Tread and tyre hardness

■■■■■ 65 Shore A

Rolling resistance



■■■■■ very good

Wear resistance

■■■■■ good

Operating noise / floor surface preservation

■■■■■ very good



Product references



Corresponding standard locking L-ALEV 200K-FI



Corresponding fixed castor B-ALEV 200K



Wheel used ALEV 200/20K