



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought


TE Part #9-1879215-7  
CPF 0402 46K4 0.1% 25PPM 1K RL

TE Part #4-1879215-0  
CPF 0402 10K7 0.1% 25PPM 1K RL

TE Part #204763-E  
SMCB 26 F AB VV 7-23 CL \* H007 137 E002

TE Part #1746311-1  
Std USB Type A, R/A, T/H





TE Part #5750477-1

5 CIRC DIN RCPT W/GRND FINGERS



TE Part #6-1879215-6

CPF 0402 22K1 0.1% 25PPM 1K RL



TE Part #5749180-1

Mini DIN, 6 pos, R/A, Shield



TE Part #4-1622825-6

RL73K 3A R27 5% 4K RL



TE Part #9-1879212-8

CPF 0402 24R9 0.1% 25PPM 1K RL

TE Part #4-174645-0

1.25FP,P10,DL,O,N,BG,5.00,6.90

Documents

Product Drawings

1.25FP,P06,DL,O,N,TR,5.00,6.90

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-176891-6\_F\_c-3-176891-6-f.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-176891-6\_F\_c-3-176891-6-f.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-176891-6\_F\_c-3-176891-6-f.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

AMP 1.25mm F-P Connector (Board To Board)

Japanese

Product Specification

Japanese