

FEATURES

- **UV Resistant:** Ensures longevity and performance in outdoor environments.
- **High Tensile Strength:** Withstands up to 80 kg, providing robust support for heavy-duty applications.
- **Wide Operating Temperature Range:** Suitable for temperatures up to 85 °C, making it versatile for different conditions.
- **Flame Retardant:** Meets UL 94 V-2 standards, enhancing safety in fire-prone areas.
- **Large Bundle Diameter:** Accommodates bundles up to 284 mm, offering flexibility in use.
- **Durable Nylon Material:** Provides strength and resistance to wear and tear.

RS PRO Heavy Duty Cable Tie, 940 mm Nylon

RS Stock No: 656-067



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Heavy Duty Cable Tie is designed for secure and reliable bundling of cables and wires. Made from durable nylon, it is ideal for industrial applications where strength and UV resistance are crucial. With a maximum bundle diameter of 284 mm, it offers flexibility and ease of use in various settings.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Heavy Duty Cable Tie
Tensile Strength	80 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	940 mm
Material	Nylon
Maximum Bundle Diameter	284 mm
Width	9 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513
---------------------	---