



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Right Angle**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Number of Rows: **1**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	3
Number of Loaded Positions	3
Number of Power Positions	3
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Right Angle



Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features

PCB Retention Feature Material	Phosphor Bronze
PCB Retention Feature Plating Material	Tin
Connector Profile	Low
Primary Product Color	Natural

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 – 2.54 µm[50 – 100 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Size	.64mm
Contact Mating Area Plating Material Thickness	2.54 – 7.62 µm[100 – 300 µin]
Mating Square Post Dimension	.64 mm[.025 in]
PCB Contact Termination Area Plating Material Thickness	2.54 – 7.62 µm[100 – 300 µin]
Contact Shape & Form	Square
Contact Layout	Inline
Contact Mating Area Length	4.15 mm[.163 in]
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab
Contact Current Rating (Max)	5 A

Termination Features

Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention	Without



Mating Alignment Type	Polarization
PCB Mount Retention Type	Hold-Down
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Mating Entry Location	Side
Housing Material	High Temperature Nylon
Centerline (Pitch)	3 mm[.118 in]

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	3.86 mm[.152 in]
Connector Length	13 mm[.512 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	215
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2-1445057-4
MICRO MNL HDR ASSY SINGLE ROW




TE Part # 1445022-3
MICRO MNL RFECEPT HSG SINGLE R




TE Part # 2315752-3
3P, MICRO MNL RCPT HSG SINGLE ROW, V0 GW




TE Part # 2029030-2
2P MICRO MNL HDR ASY SR SIDE L



TE Part # 2029102-3
3P MICRO MNL RCPT SR SIDE WHT



TE Part # 2029104-4
4P MICRO MNL HDR ASSY SR SIDE N



TE Part # 2-1445057-8
MICRO MNL HDR ASSY SINGLE ROW



TE Part # 2029104-2
2P MICRO MNL HDR ASSY SR SIDE N



TE Part # 2-1445056-3
MICRO MNL HDR ASSY SINGLE ROW

TE Part # 2008571-3
3 POS MICRO MNL, TOP LATCH, BL

TE Part # 2029030-4
4P MICRO MNL HDR ASY SR SIDE L

TE Part # 2-1445057-7
MICRO MNL HDR ASSY SINGLE ROW

TE Part # 2029030-3
3P MICRO MNL HDR ASY SR SIDE L

TE Part # 2-1445057-3
MICRO MNL HDR ASSY SINGLE ROW

TE Part # 2029047-3
3P MICRO MNL RCPT HSG SR SIDE

Also in the Series

Micro MATE-N-LOK

Connector Contacts(27)

PCB Headers & Receptacles(371)

Power Contacts(27)

Rectangular Connector Housings(98)

Rectangular Power Connectors(469)

Standard Rectangular Connectors(98)

Wire-to-Board Headers & Receptacles
(371)

Customers Also Bought

TE Part #2834010-3
SLIM CONTACT FOR WIRE 20-24AWG

TE Part #5535043-4
ASSY,RECEPTACLE,EUROCARD,TYPE

TE Part #CAT-H857-H34220
AMP HPI 2.0 mm Headers

TE Part #2-1445091-3
MICRO MNL HDR ASSY S/ROW AU LF



Documents

Product Drawings

3P MICRO MNL HDR ASY SR SIDE N

English

CAD Files

Customer View Model

ENG_CVM_CVM_2029104-3_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2029104-3_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2029104-3_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

MICRO MATE-N-LOK CONNECTOR SYSTEM

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English