


Geberit Mapress Carbon Steel reducer with plain end



Example image

APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For extinguishing water (wet)
- For sprinklers (wet)
- For compressed air (oil purity class 3)

- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Concentric
- Outside zinc-plated

- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material	Non-alloy steel 1.0034 E195 (EN 10305)
------------------	--

Art. no.	DN	d, ø mm	d1, ø mm	L cm	H cm
22301	12 / 10	15	12	5.1	3.4
22302	15 / 10	18	12	5.3	3.6
22303	15 / 12	18	15	5.5	3.5
22304	20 / 10	22	12	6	4.3
22305	20 / 12	22	15	5.9	3.9

<i>Art. no.</i>	<i>DN</i>	<i>d, ø mm</i>	<i>d1, ø mm</i>	<i>L cm</i>	<i>H cm</i>
22306	20 / 15	22	18	5.7	3.7
22349	25 / 10	28	12	6.7	5
22307	25 / 12	28	15	6.6	4.6
22308	25 / 15	28	18	6.4	4.4
22309	25 / 20	28	22	6	3.9
22310	32 / 12	35	15	7.5	5.5
22311	32 / 15	35	18	7.4	5.5
22312	32 / 20	35	22	7.1	5
22313	32 / 25	35	28	6.8	4.5
22315	40 / 15	42	18	8	6
22316	40 / 20	42	22	8.2	6.1
22317	40 / 25	42	28	8.3	6
22318	40 / 32	42	35	7.7	5.1

Art. no.	DN	d, ø mm	d1, ø mm	L cm	H cm
22320	50 / 15	54	18	9.5	7.5
22321	50 / 20	54	22	9.5	7.4
22322	50 / 25	54	28	11	8.7
22323	50 / 32	54	35	10.6	8
22324	50 / 40	54	42	9.2	6.2
22327	65 / 50	66.7	54	12.7	9.1
22330	65 / 40	76.1	42	12.7	9.7
22331	65 / 50	76.1	54	14.6	11.1
22332	65 / 65	76.1	66.7	15.1	10.1
22338	80 / 50	88.9	54	16.2	12.8
22339	80 / 65	88.9	76.1	16.1	10.8
22345	100 / 50	108	54	17.2	13.7
22346	100 / 65	108	76.1	18.4	13.1

Art. no.	DN	d, ø mm	d1, ø mm	L cm	H cm
22348	100 / 80	108	88.9	20.3	14.3