



Stud type track rollers NUKR52

(Series NUKR)

with axial guidance, full complement cylindrical roller set,
labyrinth seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system

(<http://www.ina.de/content.ina.de/en/mediathek/library/library.jsp>) or by telephone on +49 (91 32) 82 - 28 97.

D	52 mm
d ₁	20 mm Tolerance: h7
B	66 mm
B ₁ max	25,6 mm
B ₂	40,5 mm
B ₃	9 mm
C	24 mm
C ₁	0,8 mm
d ₂	31 mm
d ₃	4 mm
F _{0r} per	34000 N Permissible static radial load
G	M20x1,5
l _G	21 mm
r _{min}	1 mm
W	10 mm Nominal dimension for hexagonal socket
m	450 g Mass
MA	120 Nm Nut tightening torque
C _r w	29000 N Effective dynamic load rating as track roller (radial)
C _{0r} w	40500 N Effective static load rating as track roller (radial)
F _r per	17100 N Permissible dynamic radial load

Cur	5300 N	Fatigue limit load
w		
nD	4200 1/min	Speed (with continuous operation and grease lubrication)
G		
	NIPA2X7,5	Drive fit lubrication nipple Drive fit lubrication nipples are supplied loose. Only these lubrication nipples should be used.
AP	AP10	Suitable central lubrication adapter for connection to a central lubrication system

