



 PRODUCT-DETAILS

OS800D12-60

OS800D12-60 SWITCH FUSE



General Information

Extended Product Type	OS800D12-60
Product ID	1SCA022864R9630
EAN	6417019334677
Catalog Description	OS800D12-60 SWITCH FUSE
Long Description	Switch fuse, front operated, 3-pole, without fuse covers, shaft, handle and mounting kit not included

ABB EcoSolutions

ABB Site Meeting Group	UL 2799 Zero Waste To Landfill Validation available
Waste To Landfill Target	
Environmental Product Declaration - EPD	1SCC311202D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201

RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC311013C0201
Instructions and Manuals	1SCC311016M0210
Environmental Product Declaration - EPD	1SCC311202D0201

Environmental

Degree of Protection	acc. to IEC 60529 IP00
----------------------	------------------------

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Weight	12.5 kg
--------------------	---------

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	328 mm
Package Level 1 Depth / Length	365 mm
Package Level 1 Height	260 mm
Package Level 1 Gross Weight	13.3 kg
Package Level 1 EAN	6417019334677

Technical

Conventional Free-air Thermal Current (I_{th})	$\Theta = 40\text{ °C}$ 800 A
Conventional Thermal Current (I_{the})	Fully Enclosed 720 A
Degree of Protection	acc. to IEC 60529 IP00
Fuse Size	NH2 NH3
Fuse System	DIN
Handle Type	Handle not included
Mounting Type	Base mounting
Number of Poles	3P
Operating Mode	Front
Power Loss	at Rated Operating Conditions per Pole 75 W
Rated Conditional Short-Circuit Current (I_{nc})	(500 V) 100 kA (690 V) 80 kA

Rated Insulation Voltage (U _i)	1000 V
Rated Operational Power AC-23A (P _e)	(220 ... 240 V) 250 kW (400 V) 450 kW (415 V) 450 kW (500 V) 560 kW (690 V) 710 kW
Rated Operational Voltage	Main Circuit 690 V AC
Rated Short-time Withstand Current Low Voltage (I _{cw})	for 1 s 18 kiloampere rms
Standards	IEC 60947-3
Terminal Type	Lug terminals
Tightening Torque	50 ... 75 N·m

Technical UL/CSA

Tightening Torque	50 ... 75 N·m
--------------------------	----------------------

Certificates and Declarations

A2L Certificate - IEC	1SCC311209D0201
ATEX Certificate	No certification needed
Declaration of Conformity - CE	1SCC311112D2704
DNV GL Certificate	1SCC311131D0203
UL Certificate	No certification needed

External Classifications and Standards

ETIM 9	EC001040 - Fuse switch disconnecter
ETIM 10	EC001040 - Fuse switch disconnecter
UNSPSC	39122233
IDEA Granular Category Code (IGCC)	5291 >> Fuse switch disconnecter
eClass	V11.1 : 27371401
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Fuses

