

Inductive proximity sensors XS, inductive sensor XS7 80x80x26, PBT, Sn40mm, 12...24 VDC, M12

XS7D1A1DAM12

Main

Range of product	Telemecanique Inductive proximity sensors XS	
Series name	General purpose	
Sensor type	Inductive proximity sensor	
Device application	-	
Sensor name	XS7	
Sensor design	Flat form 80 x 80 x 26	
Size	26 mm	
Body type	Fixed	
Detector flush mounting acceptance	Flush mountable	
Material	Plastic	
Enclosure material	PBT	
Type of output signal	Discrete	
Wiring technique	2-wire	
Discrete output function	1 NO	
Output circuit type	DC	
Electrical connection	4 pins M12 male connector, pin assignment : 3-4	
[Us] rated supply voltage	1224 V DC with reverse polarity protection	
Switching capacity in mA	1.5100 mA DC with overload and short-circuit protection	
IP degree of protection	IP67 double insulation conforming to IEC 60529	

Complementary

Detection face	Frontal	
Front material	PBT	
Operating zone	032 mm	
Differential travel	115% of Sr	
Status LED	Output state: 1 LED (yellow)	
Supply voltage limits	1036 V DC	
Maximum residual current	0.5 mA open state	
-		

Switching frequency	<= 100 Hz
Maximum voltage drop	<4 V (closed)
Maximum delay first up	10 ms
Maximum delay response	10 ms
Maximum delay recovery	10 ms
Marking	CE
Depth	26 mm
Height	80 mm
Width	80 mm

Environment

Product certifications	UL Ecolab C-Tick CSA	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	25 gn amplitude = +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn for 11 ms conforming to IEC 60068-2-27	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	316.0 g
Package 1 Height	4.2 cm
Package 1 width	9.5 cm
Package 1 Length	13.2 cm
Unit Type of Package 2	S02
Number of Units in Package 2	22
Package 2 Weight	7.427 kg
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product	
REACh Regulation	REACh Declaration	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
Mercury free	Yes	
RoHS exemption information	Yes	
Environmental Disclosure	Product Environmental Profile	
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go www.P65Warnings.ca.gov	

Contractual warranty


Warranty	18 months
warranty	10 1110111115

Product data sheet

XS7D1A1DAM12

Dimensions Drawings

Dimensions




XS7D1A1DAM12

Mounting and Clearance

Setting-up


Minimum Mounting Distances (mm)

Side by Side




e (1) ≥ 120

Face to Face



e (2) ≥ 300

Facing a Metal Object



e (3) ≥ 120


Product data sheet

XS7D1A1DAM12

Connections and Schema

Wiring Schemes

2-Wire NO



M12

