IEL+x SOFT

ELESA original design

Two-volume revolving handles



SOFT

Material

High resilience polypropylene based (PP) technopolymer, coated with "soft-touch" thermoplastic elastomer (TPE) chemically bonded, hardness 70 Shore A.

The coating material is certified in compliance with FDA (U.S. Food and Drug Administration).

Resistant to solvents, oils, greases and other chemical agents.


- Colour
- Black, matte finish. • Standard executions
- Zinc-plated steel shank, hexagon socket at threaded end.
- IEL+x: without ring.
- IEL+x-A: with matte anodised aluminium ring (ELESA original design). *Features and applications*

The coating, with "soft-touch" elastomer, improves the grip even in the presence of oils, greases and sweat from the hand. For this reason it is suitable for fitness machines, tools and machines for gardening and goods transport, high-precision instruments and disability aids.

Special executions on request

IEL+x-H: with magnifying lens for labels with marks and symbols.





Code	Description	D	L	d _{6g}	dı	I	S	$\Delta \Delta$
26651	IEL.47+x-M10 SOFT	45	47	M10	28	17	5	80
26679	IEL.65+x-M8 SOFT	45	65	M8	23	17	5	102
26681	IEL.65+x-M10 SOFT	45	65	M10	23	17	5	99
26691	IEL.65+x-M10-A SOFT	45	65	M10	23	17	5	99

