



**FAG****61901-HLC**

Deep groove ball bearing

Deep groove ball bearing 619, single row,
steel sheet metal cageSchaeffler ID:
0554609500000

Technical information



Your current product variant

Logistical code	HLC	-
Sealing	Without	Not sealed
Cage	J	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	12 mm	Bore diameter
D	24 mm	Outside diameter
B	6 mm	Width
C _r	2.890 N	Basic dynamic load rating, radial
C _{0r}	1.460 N	Basic static load rating, radial
C _{ur}	77 N	Fatigue load limit, radial
n _G	45.000 1/min	Limiting speed
n _{gr}	23.300 1/min	Reference speed
m	12 g	Weight



Mounting dimensions

$d_{a\min}$	14 mm	Minimum diameter shaft shoulder
$D_{a\max}$	22 mm	Maximum diameter of housing shoulder
$r_{a\max}$	0,3 mm	Maximum fillet radius

Dimensions

$r_{\min}$	0,3 mm	Minimum chamfer dimension
D_1	20,3 mm	Shoulder diameter outer ring
d_1	16 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

f_0	14,5	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed